


NOTES:

1. **WARNING:** This drawing does not illustrate the installation methods required for hazardous locations. Prior to any installation in a Classified Hazardous Location, verify installation methods by the Control Drawing referenced on the product's name tag and national and local codes.
2. To access the termination boards of the NGC and IMV, remove the enclosures rear covers.
3. The RS-485 bus must be wired in a daisy-chain configuration. Star configurations are not allowed.
4. Maximum accumulated length for the RS-485 bus is 4000 feet.



REF: N/A

ABB	TOTALFLOW Products	ACTION	DOC TYPE	TITLE	DWG NO.	REV	SHEET
		D24201	UD	NGC8200 PORT 2 (RS-485) TO IMV25 MULTIVARIABLE (1641200) W/RTD PROBE	2104267	AB	1 OF 1