

Technical Data Sheet

# TruFit Power Distribution Unit (PDU)

50 – 300 kVA



---

# About this document

---

## Document information

<b>File name</b>	:	ABB_PDU_TDS_TFT_50-300KVA_REV-C
<b>Model</b>	:	50 – 300kVA TruFit PDU - UL
<b>Date of issue</b>	:	10/29/2020
<b>Issued by (department)</b>	:	Product Marketing
<b>Checked by (department)</b>	:	R&D Engineering
<b>Article number</b>	:	...
<b>Document number</b>	:	TDS-PDU-MK-0146
<b>Revision</b>	:	REV-D
<b>Revision date</b>	:	3-01-2021

# Contents

1	Introduction.....	4
1.1	Key features and benefits .....	4
1.2	Mechanical characteristics.....	5
1.3	General specification.....	6
1.4	Environmental characteristics .....	6
2	Electrical characteristics .....	7
2.1	Transformer.....	7
2.2	Main input circuit breaker .....	7
3	Output/distribution specifications.....	8
3.1	Panelboard distribution.....	8
3.2	Sub-feed circuit breakers .....	8
4	PowerView metering and monitoring .....	9
4.1	Features and functionalities.....	9
4.2	PowerView Branch Circuit Management (BCM).....	10
4.3	PowerView Sub-feed Circuit Management (SFCM).....	10
5	Control and communications.....	11
5.1	System display .....	11
5.2	Communications interfaces .....	11
6	Options.....	12
6.1	Electrical options.....	12
6.2	Mechanical options.....	12

---

# 1 Introduction

ABB TruFit 50 – 300kVA PDU is a three-phase power conditioning unit for distribution of computer grade power to data processing equipment and other critical loads. Equipped with DOE 2016 compliant, high-efficiency transformers and an innovative metering/monitoring system, the TruFit PDU reliably provides clean power to critical loads.

---

## 1.1 Key features and benefits



**SACE Tmax XT breakers** provide true reliability through extreme breaking capacity in compact frames ensuring safe and reliable interruption of faults.



**Front access only design** enables better fit and optimal usage of valuable white space through elimination of side or rear clearances for all configurations.



**Innovative, centralized monitoring solution** with optional integrated thermal monitoring provides a more holistic view of equipment health/fitness.



**Compartmentalized design** helps minimize exposure to potential arc flash events and ensures routine services can be conducted quickly and safely without exposure to hazardous voltage.



**Improved sustainability** through high-efficiency, DOE 2016 compliant transformers and revenue-grade metering accuracy down to the sub-feed or branch circuit level to provide users the visibility required to optimally balance loads and maximize utilization.



### Key applications

- Data centers
- Healthcare facilities
- Financial institutions
- Colleges/Universities



## 1.3 General specification

<b>Standards</b>	ETL listed to UL 891
<b>Audible noise level</b>	NEMA ST20
<b>Access requirements</b>	Front only for installation, operation, and maintenance
<b>Degree of protection against hazards and water ingress</b>	IP20
<b>Cooling</b>	Convection cooled
<b>Ventilation</b>	Perforated top and bottom plates (optional vented kickplates for non-raised floor installations)
<b>PDU frame cabinet color</b>	RAL 9005 (black)
<b>Transport</b>	On pallet Cabinet suitable for handling by forklift
<b>Mounting</b>	Floorstand mounting holes provided
<b>Cable entry</b>	Top and/or bottom

## 1.4 Environmental characteristics

<b>Ambient operating temperature range</b>	[° F/° C]	32 - 104° F / 0 - 40° C
<b>Ambient non-operating temperature range</b>	[° F/° C]	-13 - 131° F / -25 - 55° C
<b>Relative humidity range</b>	[%]	10 - 95%, non-condensing
<b>Altitude without de-rating</b>	[ft/m]	Up to 3280 ft / 1000 m
<b>Altitude with de-rating</b>	[ft/m]	3609 ft / 1100 m: -3% 3937 ft / 1200 m: -6% 4265 ft / 1300 m: -9% 4593 ft / 1400 m: -12%

## 2 Electrical characteristics

### 2.1 Transformer

<b>kVA rating</b>	[kVA]	50, 75, 125, 150, 225, 300
<b>Input/primary voltage</b>		480 VAC, 3-phase, 3-wire + ground
<b>Input voltage window</b>		+/-10%
<b>Output/secondary voltage</b>		208/120 VAC, 3-phase, 4-wire + ground
<b>Winding material</b>		Aluminum (std.), Copper (opt.)
<b>Input/output frequency</b>	[Hz]	60 +/-5% (57 – 63Hz)
<b>Efficiency</b>		DOE 2016 compliant
<b>Percent Impedance</b>	[%]	2.5 – 5.0
<b>Percent reactance</b>	[%]	2.0 – 4.2
<b>Voltage THD (added)</b>		1% max.
<b>Insulation class</b>		Class 220
<b>Temperature rise</b>	[°C]	150
<b>Inrush</b>		11x
<b>K-rating</b>		K4 (std.), K13 & K20 (opt.)
<b>Compensation taps</b>		(2) 5% full load compensation taps, (1) above & (1) below nominal
<b>Core temperature setpoints</b>	[°C]	190 – warning/alarm, 220 – overtemperature shutdown

### 2.2 Main input circuit breaker

		50kVA	75kVA	125kVA	150kVA	225kVA	300kVA
<b>Amp setting</b>	[A]	80	125	200	225	350	450
<b>Trip unit</b>		Thermal-magnetic (std.), Electromagnetic LSI (opt.) * 300kVA main breaker available with electromagnetic LSI (ekip dip LSI) trip unit only.					
<b>Interrupt rating @ 480V</b>	[kAIC]	65					
<b>Accessories</b>		Internal 24VDC shunt trip mechanism interfaced to both local and remote EPO. * Customer shall provide dry contacts for remote EPO					

## 3 Output/distribution specifications

### 3.1 Panelboard distribution

Panelboard types/brand		GE by ABB 42-pole, ABB ProLine 42-pole
Panelboard voltage rating	[V]	GE by ABB – up to 240 ABB ProLine – up to 480
Panelboard short circuit rating	[kAIC]	GE by ABB – up to 10 ABB ProLine – up to 35
Panelboard and main breaker rating	[A]	225A, 400A
Secondary main breaker rating	[%]	80 (std.), 100 (opt.)
Secondary main breaker trip unit		Thermal-magnetic (std.), Electromagnetic LSI (opt.)
Branch circuit breaker poles	[poles]	1, 2, 3
Branch circuit breaker ratings	[A]	15 – 100 * <i>ABB ProLine branch breakers &gt;50A are side-specific</i>
Branch circuit breaker rating	[%]	80%
Branch circuit breaker trip unit		Thermal-magnetic
Branch circuit breaker type		Bolt-on

### 3.2 Sub-feed circuit breakers

		ABB Tmax XT3	ABB Tmax XT4	ABB Tmax XT5
Poles		3	3	3
Amp rating	[A]	225A	250A	400A
Rated voltage	[V]	600Y/347	600	600
Short circuit interrupt ratings	[kAIC @ 240V]	50	65	65
	[kAIC @ 480V]	25	25	35
Trip unit options	Thermal-magnetic (TMF)	Standard	Standard	Standard
	Thermal-magnetic (TMA)		Optional	Optional
	Ekip Dip		Optional	Optional
Sub-feed breaker rating	[%]	80 (std.), 100 (opt.)	80 (std.), 100 (opt.)	80 (std.), 100 (opt.)
UL current limiting compliant		No	Yes	Yes
Mechanical life	[# operations]	25,000	25,000	20,000



## 4 PowerView metering and monitoring

### 4.1 Features and functionalities

Features	PowerView Core	PowerView Pro
<b>Basic metering/monitoring</b>		
<ul style="list-style-type: none"> <li>Primary &amp; secondary of transformer (PSB)</li> </ul>	Standard	Standard
<ul style="list-style-type: none"> <li>Branch circuit management (BCM)               <ul style="list-style-type: none"> <li>Up to (4) 42p panelboards (252 circuits)</li> </ul> </li> </ul>	Optional	Optional
<ul style="list-style-type: none"> <li>Sub-feed circuit management (SFCM)               <ul style="list-style-type: none"> <li>Up to (16) 3-wire or 4-wire sub-feed breakers</li> </ul> </li> </ul>	Optional	Optional
<b>Monitoring system standard parameters</b>		
<ul style="list-style-type: none"> <li>Voltage-current RMS</li> <li>MIN current</li> <li>MAX current</li> <li>kW (power)</li> <li>kWh</li> <li>kVAr</li> <li>kVA-load</li> <li>kVAh</li> <li>Max energy demand</li> <li>Power factor (PF)</li> <li>Crest factor</li> <li>Total harmonic distortion (THD) up to 9<sup>th</sup> order</li> </ul>	Standard	Standard
<b>Accuracy</b>	+/-2%	+/-1%
<b>Harmonics measurements</b>	Up to 9 <sup>th</sup> order	Up to 35 <sup>th</sup> order
<b>Waveform capture</b>	Not available	Standard
<b>Custom circuit naming/numbering</b>	Not available	Standard
<b>Custom grouping of circuits</b>	Not available	Standard
<b>Global time synch via NTP</b>	Not available	Standard
<b>Breaker status monitoring (open, closed, tripped) via Discrete Input Board (DIB)</b>	Not available	Optional
<b>Integrated thermal monitoring via Thermocouple Interface Board (TIB)</b>	Not available	Optional

---

## 4.2 PowerView Branch Circuit Management (BCM)

---

### BCM features/specifications

---

True RMS current, peak current (resettable), minimum current (resettable) for each branch circuit

---

Panel board phase current

---

Voltage, power, energy, power factor and THD (current) for each branch circuit

---

Voltage, power, energy, power factor and THD (current) at the panel board level

---

User configurable warning and alarm thresholds for each circuit

---

User configurable warning and alarm statuses for each circuit

---

---

## 4.3 PowerView Sub-feed Circuit Management (SFCM)

---

### SFCM features/specifications

---

Real time current, peak current (resettable), minimum current (resettable) for each sub-feed circuit

---

Voltage, power, energy, power factor and THD (current)

---

User configurable warning and alarm thresholds for each sub-feed circuit

---

User configurable warning and alarm statuses for each sub-feed circuit

---

---

## 5 Control and communications

---

### 5.1 System display

---

The PDU Control Panel is a 6.5" color, touch screen graphical display which provide the following information to the user:

- Mimic diagram indication PDU status
  - PDU measurements
  - History of events (alarms and messages)
  - PDU settings
  - Operation command
- 

---

### 5.2 Communications interfaces

---

Modbus over RTU (via RS485)	Standard
Modbus over TCP (via Ethernet)	Standard
Serial service port (via USB)	Standard
Customer download port (via USB)	Standard
Local EPO interfaced to main input breaker shunt trip	Standard
Remote EPO - Emergency Power OFF (n/c contact, customer supplied)	Standard
User Interface Board (UIB)	Standard ( <i>see UIB image in section 5.2.1 for additional details</i> )

---

---

## 6 Options

---

### 6.1 Electrical options

- 
1. 40kA primary SPD
  2. 40kA secondary SPD
  3. Isolated grounds for panelboards
- 

---

### 6.2 Mechanical options

- 
1. Vented kick-plates for non-raised floor installations
  2. Seismic rated under-floor floorstands (12" – 60"H)
  3. Heavy duty swivel casters
-



<https://new.abb.com/ups/power-distribution>

—  
**ABB Inc.**

5900 Eastport Boulevard  
Richmond, VA 23231  
USA



© Copyright 2021 ABB. All rights reserved.

Specifications subject to change without notice.

The information contained in this publication is intended solely for the purposes indicated. The present publication and any other documentation supplied with the UPS system is not to be reproduced, either in part or in its entirety, without the prior written consent of ABB.

Changes to the product or to the information contained in this document are reserved; so are errors and omissions. Please reference ABB order confirmations and submittal documentation packages for job specific configurations.