



NOTE: INTERNAL SCHEMATIC FOR  
PCMU STYLES R445\_ \_ X

4	5		INTERPRET GEOMETRIC TOLERANCE PER: ASME Y14.5- 2009	THIRD ANGLE PROJECTION 	The information contained in this document has to be kept strictly confidential. Any unauthorized use, reproduction, distribution or disclosure to third parties is strictly forbidden. ABB reserves all rights regarding Intellectual Property Rights.	DFTI/DATE: K. MARGIOTTA 12/03/13 CHKR/DATE: P. SHAH 12/03/13 APPR/DATE: B. TAUZER 12/04/13	<b>ABB</b>		
ECO CSENG-3103	ECO CSENG-4083	UNLESS OTHERWISE SPECIFIED.	Dimensions are in inches. Tolerances: One Place Decimal: ±0.020 (.5) Two Place Decimal: ±0.010 (.25) Three Place Decimal: ±0.005 (.13) Four Place Decimal: ±0.003 (.07) Angular: ±1°		SOFTWARE TYPE: <b>AUTOCAD 2011</b>	TITLE: <b>DPU445 TO REF615 PCMU 445 SCHEMATIC</b>			
		ENG. REF:			Copyright 2017 ABB All rights reserved		SIZE <b>A</b>	DWG. NO: <b>95A1075</b>	REV: <b>5</b>
		ABB Protective Relays and Switches, Coral Springs FL, U.S.A.			SCALE: NTS	SHEET 1 OF 1			