



Type Test Report					Date of issue: 2011.12.19						
Customer:					Serial No.: 3GE105113S7723						
					Type: M3AA 132MB 6					Product Code: 3GAA133443-GE	
Customer ref.:											
Rating:					V	Hz	kW	r/min	A	cos φ	Duty
3~Motor					415	Y 50	4,00	980	11,10	0,58	S1
Insul.cl.F											
IP55											
Eff class IE2					50Hz : IE2 - 85,9(100%) - 84,6(75%) - 81,2(50%)						
Resistance					Insulation resistance at 25 °C					Overload	
Line					R > 2000 Mohm 1000 V					Current 150 % 120s	
U ₁ - V ₁					Ambient: 18,0 °C					Torque 160 % 15s	
U ₁ - W ₁					1,37000 Ω					Speed 120 % 120s	
V ₁ - W ₁					1,37200 Ω						
					1,37300 Ω						
					High-voltage test winding 2400 V					60 s	
Test	Torque [Nm]	Line U[V]	f[Hz]	Input I[A]	P1 [kW]	Output P2 [kW]	n[r/min]	cos φ	η [%]		
No load test		415 Y	50	8,5	0,39		1000	0,06			
Locked rotor test		112,2 Y	50	13,3	0,97		0	0,38			
Thermal test (100% load)	39,0	415 Y	50	11,1	4,66	4,00	980	0,58	85,90		
Partial load points:											
~75% load	29,1	415 Y	50	9,8	3,55	3,00	985	0,50	84,60		
~50% load	19,3	415 Y	50	8,7	2,46	2,00	990	0,39	81,20		
~25% load	9,6	415 Y	50	8,2	1,42	1,00	995	0,24	70,40		
Temperature rise at rated load.					°C	K	Method		Measurement method		
Stator winding :					37,0	3			1 Resistance		
Frame :					21	3			2 Thermometer		
Bearing D-end :					24,4	3			3 Thermocouples		
Ambient Temperature :					25	3					
Manufactured and tested in accordance with rules of IEC 60034-1 and IEC 60034-2-1.											
PLL determined from residual loss.											
On behalf of customer											
On behalf of manufacturer			Date of test			1.2.2011					
Tested by Asea Brown Boveri, S.A., Fabrica Motores , 08192 Sant Quirze del Valles , Spain								Telephone		+34 93 728 85 00	
								Telefax		+34 93 728 85 33	

Computer print-out valid without signature.