

ABB MEASUREMENT & ANALYTICS | DATA SHEET

# TB84TE

## 2-electrode conductivity transmitter



---

## **Measurement made easy**

Superior accuracy in low conductivity and pure water applications

### **Smart key menu programming**

Superior accuracy in low conductivity and pure water applications

### **Two fully programmable isolated outputs**

- 0 to 20 mA or 4 to 20 mA

### **Three fully programmable relay outputs**

### **Adjustable damping**

### **Hold output function**

- holds all outputs or any individual output

### **Programmable security codes and configuration lockout**

### **Universal power supply**

- 120 / 240 V AC, 50 / 60 Hz. Voltage range is 94 to 276 V AC

### **NEMA 4X/IP65 housing**

- cast aluminum with corrosion-resistant polyester powder coat finish

### **FM and CSA non-incendive agency approvals**

- CE Mark

## Advantage 2-wire, 2-electrode conductivity transmitter

The ABB TB84TE Advantage™ conductivity transmitter is a unique and advanced microprocessor-based instrument. Smart keys on the front panel provide local programming of all analyzer functions. Easy-to-follow instructions appear above each smart key. A secondary display clearly defines each menu option during programming. When the analyzer is in the normal operating mode, the secondary display shows several useful parameters. This innovative, user-friendly interface provides straightforward analyzer operation, configuration, and calibration.

Standard outputs include two isolated analog (current) outputs and three relay outputs. The analog outputs can be configured for the process variable (PV) and / or temperature. The relay outputs can be configured for the PV, temperature, diagnostics, cycle timer controller, or sensor cleaner.

The TB84TE transmitter is compatible with all ABB 2-electrode conductivity sensors. It automatically ranges itself across three decades of conductivity resolution for any single cell constant. 2-electrode sensors provide accurate conductivity measurements in lower conductivity solutions and pure water. Precalibration is accomplished by programming the cell constant of the sensor during configuration. Careful selection of electrode materials (316 stainless steel standard), insulator materials and electrode spacing provides rugged sensors and reduced sensor maintenance. Sensor diagnostics include sensor polarization, and open or shorted temperature compensator / cabling.

The TB84TE transmitter meets current CE and NEMA 4X/IP65 requirements.

## 2-electrode sensor compatibility

The transmitter accepts inputs from all ABB 2-electrode sensors. A menu choice during configuration makes changing from one cell constant to another easy. No jumpers or manual adjustments are required.

## 2-electrode sensor ranges

Cell Constant	Conductivity range	Display resolution	Autorange
0.01	0 to 199 $\mu\text{S}/\text{cm}$	0.001 $\mu\text{S}/\text{cm}$	1.999 to 19.99 to 199.9 $\mu\text{S}/\text{cm}$
0.10	0 to 1,999 $\mu\text{S}/\text{cm}$	0.01 $\mu\text{S}/\text{cm}$	19.99 to 199.9 to 1,999 $\mu\text{S}/\text{cm}$
1.00	0 to 19.99 $\text{mS}/\text{cm}$	0.1 $\mu\text{S}/\text{cm}$	199.9 to 1,999 $\mu\text{S}/\text{cm}$ to 19.99 $\text{mS}/\text{cm}$

## Basic or advanced programming

Basic or advanced programming modes can be chosen at the time of purchase. Advanced mode has an expanded set of functions intended for complex applications. Separating basic and advanced modes simplifies setup and calibration activities. Advanced configuration choices are:

- Concentration analyzer:
  - User-defined through a 6-point conductivity versus concentration linear curve fit where output follows concentration
- Temperature compensation types:
  - Pure water neutral salt
  - Pure water trace base
  - Pure water trace acid
  - User-defined function generator
- Analog pulse diagnostic output
- Nonlinear output:
  - User-defined through a 6-point conductivity versus desired current output that best fits the nonlinear relationship
- Expanded relay functions and flexibility

## Analog outputs

The transmitter has two isolated analog outputs (AO1 and AO2). Each is user-configurable as either a 0 to 20 or a 4 to 20 mA signal. AO1 is dedicated to the PV while AO2 is configurable for either the PV or temperature. A 2-point calibration method applies to both analog outputs. This enables adjustment of the analog outputs to compensate for other devices in the loop that may not be calibrated. Entering the PV or temperature endpoints in reverse order allows for reverse-acting outputs.

A capacitive type lag, applied via the damping function, is useful in process environments where noise is present. Damping is supported for both analog outputs and the displayed PV and has a maximum value of 99.9 seconds. One damping value affects both analog outputs and the displayed PV in basic configuration. Individual damping values affect each analog output and the displayed PV in advanced configuration.

## Relay outputs

The transmitter has three relay outputs available (RO1, RO2, RO3). Each is jumper selectable as either NO (normally open) or NC (normally closed). RELAY, followed by the corresponding relay number appears on the display when a relay activates. The functionality of each relay output depends on the configuration mode. Table 1 shows the possible functionality of each relay output for basic and advanced configuration. Advanced programming enables all function choices shown in Table 1 for each of the three relay outputs.

Function	R01		R02		R03	
	Basic	Adv	Basic	Adv	Basic	Adv
High or low PV alarm	✓	✓	✓	✓	✓	✓
High or low temperature alarm (°C or °F)		✓	✓	✓	✓	✓
Diagnostics alarm		✓		✓	✓	✓
High- or low-cycle timer		✓		✓		✓
Sensor cleaner*		✓		✓		✓

\* If a relay output is configured as a sensor cleaner, no other relay output can be used for this function

Table 1 Relay output functionality

High and low alarms can be chosen for the PV and temperature in either °C or °F. Each has a user-selectable deadband and time delay designed to control relay functions and prevent problems like relay chatter. The diagnostic relays are linked to all diagnostic conditions. The high- and low-cycle timer has adjustable set points, cycle time and on time. The cycle timer provides a waiting period to see the results of chemical addition by interrupting the feed. The sensor cleaner feature provides for cycle time, on time and recovery time programming. This makes set up and operation of the transmitter with the ABB hydraulic sensor cleaner or TB18 Safe-T-Clean® sensor valve easy and trouble-free.

## Diagnostics

The TB84TE transmitter monitors both the sensor and the transmitter constantly. This helps to ensure reliability and accuracy. Upon detection of a diagnostic condition, the transmitter provides diagnostic notification by flashing a FAULT icon on the display and supplying a pulse on AO1 (if activated). Pressing the FAULT info smart key stops the icon from flashing and provides, on the secondary display, a short description and fault code. The FAULT icon remains on until the problem is resolved. Sensor faults that activate the diagnostic notification are:

- Sensor polarization
- Shorted or open temperature compensator

## Hold output

The transmitter has a hold output state that improves plant safety and process integrity during maintenance and calibration. When activated, HOLD appears at the top of the display. Upon release of the hold state, HOLD disappears. The analog outputs can be held to any preselected level. The relay outputs can be held individually to any active or inactive state. This is useful for checking and exercising any external devices connected to the transmitter. When the sensor cleaner option is chosen, the transmitter provides the option of holding all analog and relay outputs during the cleaning cycle.

## Diagnostic pulse

The analog output is fully scalable over any conductivity or concentration range. Advanced configurations enable pulsing of AO1 during a diagnostic condition.

When the diagnostic pulse is active, the output is modulated for 1 second out of a 6-second repeating cycle to a configuration selectable level ranging from 1 to 100 % of span (0.16 to 16 mA for a 4 to 20 mA output or 0.20 to 20 mA for a 0 to 20 mA output). Should the actual output of the transmitter be below 12 mA, the pulse will add current; if the actual output is at or above 12 mA, it will subtract current. This provides remote notification of a problem with proper configuration of a digital control system (DCS), programmable logic controller (PLC), or chart recorder.

## Temperature compensation

The TB84TE transmitter is compatible with Pt100 or Pt1000 temperature compensators. The automatic temperature compensation options are:

- manual
- automatic for potassium chloride (KCl),
- user-entered coefficient in %/°C
- a user-defined function generator
- trace acid
- trace base
- neutral salt for pure water

## Calibration

Smart key programming makes analyzer calibration accurate and efficient. Process calibration is a straight-forward 1-point smart calibration resulting in either a slope adjustment, offset adjustment, or a combination of adjustments. Selecting the reset calibration state results in the calibration defaulting to the original factory calibration. A 1-point smart temperature calibration is also available. This calibration adjusts either the temperature slope, offset, or a combination. A special edit calibration state enables manual editing or adjustment of the calibration data. This feature is useful during a startup where a large number of similar loops are being set up and calibrated at the same time.

Calibration of the 0 to 20 or four to 20 mA output is provided via an easy 2-point procedure.

## Programmable security code

The transmitter has a single three-digit security code. Menu-selectable choices enable the security code to be applied to none or any combination of the following menu choices:

- calibrate
- output / hold
- set point / tune
- configure

## Specification

### Type

Conductivity transmitter

### Input voltage

120 / 240 V AC, 50 / 60 Hz

### Range

94 to 276 V AC

### Installation category

II

### Power consumption

17 VA max.

### Input type

ABB 2-electrode conductivity sensors

### Input Range

Conductivity

0.000  $\mu\text{S}/\text{cm}$  to 19.99  $\mu\text{S}/\text{cm}$

Concentration

0.000 to 1,999 digits (engineering units configurable)

### Display resolution

Conductivity

0.001  $\mu\text{S}/\text{cm}$ , 0.01  $\mu\text{S}/\text{cm}$ , 0.1  $\mu\text{S}/\text{cm}$   
(cell constant dependent)

Concentration

0.001 digits (configurable)

Temperature

1  $^{\circ}\text{C}$ , 1  $^{\circ}\text{F}$

### Temperature compensation types

- Pt100
- Pt1000

### Temperature compensation

- Manual (0.1N KCl based)
- Automatic, configurable as:
  - standard (0.1N KCl based)
  - user-defined coefficient (0 to 9.99 %/ $^{\circ}\text{C}$ )
  - user-defined function generator
  - pure water (neutral salt)
  - pure water (acid)
  - pure water (base4)

## ...Specification

### Analog output ratings

2, completely isolated 0 to 20 and 4 to 20 mA outputs, 750  $\Omega$  max. load value, AO1 fixed to PV, AO2 configurable to either PV or temperature

#### AO1

Conductivity / concentration – isolated 0 to 20 and 4 to 20 mA, direct or reverse-acting, linear and nonlinear, configurable across full range

##### Minimum span

- 1.00 cell constant 100.0  $\mu\text{S}/\text{cm}$
- 0.10 cell constant 10.00  $\mu\text{S}/\text{cm}$
- 0.01 cell constant 1.000  $\mu\text{S}/\text{cm}$
- Concentration 5 % max. concentration range

##### Maximum span

- 1.00 cell constant 19.99 mS/cm
- 0.10 cell constant 1,999  $\mu\text{S}/\text{cm}$
- 0.01 cell constant 199.9  $\mu\text{S}/\text{cm}$
- Concentration 1,999 digits

#### AO2

Conductivity / concentration / temperature ( $^{\circ}\text{C}$  or  $^{\circ}\text{F}$ ) – isolated 0 to 20 and 4 to 20 mA, direct or reverse-acting, configurable across full range

##### Minimum span

- 1.00 cell constant 100.0  $\mu\text{S}/\text{cm}$
- 0.10 cell constant 10.00  $\mu\text{S}/\text{cm}$
- 0.01 cell constant 1.00  $\mu\text{S}/\text{cm}$
- Concentration 5 % max. concentration range
- Temperature 10  $^{\circ}\text{C}$ , 18  $^{\circ}\text{F}$

##### Maximum span

- 1.00 cell constant 19.99 mS/cm
- 0.10 cell constant 1,999  $\mu\text{S}/\text{cm}$
- 0.01 cell constant 199.9  $\mu\text{S}/\text{cm}$
- Concentration 1,999 digits
- Temperature 300  $^{\circ}\text{C}$ , 540  $^{\circ}\text{F}$

### Relay outputs

Form C, SPDT relays that are jumper selectable as either normally open or normally closed. Refer to Table 1 on page 4 to see the functionality of each relay output in basic and advanced configuration.

#### Contact ratings (max.)

AC	100 VA, 240 V AC, 3 A
DC	50 W, 24 V DC, 2 A

#### High and low set points (basic and advanced configuration)

Source: conductivity and concentration

- High/low/deadband Software configurable
- Delay value range 00.0 to 99.9 min.

Source: temperature ( $^{\circ}\text{C}$  or  $^{\circ}\text{F}$ )

- High and low range 0 to 300  $^{\circ}\text{C}$  or 32 to 572  $^{\circ}\text{F}$
- Deadband range 0 to 10  $^{\circ}\text{C}$  or 0 to 18  $^{\circ}\text{F}$
- Delay value range 00.0 to 99.9 min

#### High- or low-cycle timer (advanced configuration only)

##### Sensor cleaner (advanced configuration only)

- Cycle time range 00.0 to 99.9 h
- On time range 00.0 to 99.9 min
- Recovery time range 00.0 to 99.9 min
- Turn on range Software configurable

## Nonlinearity and repeatability

### Conductivity

- Display  $\pm 1.0$  % of measurement range per decade
- Output  $\pm 0.02$  mA at full scale output settings
- Temperature 1 °C

## Maximum sensor cable length

30.5 m (100 ft)

## Turn on time

2 s typical, 4 s max.

## Load resistance range (analog outputs)

750  $\Omega$  max.

## Damping

Continuously adjustable from 00.0 to 99.9 s

## Dynamic Response

3 s for 90 % step change with 00.0 s damping

## Mounting position effect

None

## Environmental (temperature)

### Operating

-20 to 60 °C (-4 to 140 °F)

### Storage

-40 to 70 °C (-40 to 158 °F)

### Humidity (operating and storage)

Will meet specifications to 95 % RH

## Housing

NEMA 4X and IP65, anodized aluminum alloy with corrosion-resistant polyester powder coating

### Conduit connection

5 total, 2 each 22.2 mm (0.875 in) holes in enclosure that accept ½ in hubs, 3 each 15.24 mm (0.6 in) holes that accept PG9 hubs

### Size (½ DIN), H x W x D

144.0 x 144.0 x 171.0 mm (5.67 x 5.67 x 6.73 in)

### Min. panel depth

144.8 mm (5.70 in)

### Max. panel thickness

9.5 mm (0.38 in)

### Panel cutout

135.4 (+1.3, -0.8) by 135.4 (+1.3, -0.8) mm  
(5.33 [+0.05, -0.03] by 5.33 [+0.05, -0.03] in)

### Weight

2.1 kg (4.6 lb)

3.4 kg (7.5 lb) with pipe mounting hardware

## Agency certifications

### CSA

- Class I, Division 2, Groups A, B, C, and D
- Class II, Division 2; Groups E, F and G
- Class III, Division 2

### FM

Non-incendive:

- Class I, Division 2, Groups A, B, C, and D
- Class II, Division 2; Groups F and G
- Class III, Division 2


### EMC requirements

CE Certified – complies with all applicable European Community product requirements, specifically those required to display the CE markings on the product nameplate.


## Installation

Dimensions in mm (in)


### Panel-mounting




### Hinge / Wall (rear) mounting




**Wall (side) mounting**



**Pipe-mounting**



## Electrical connections



## Ordering information

Advantage conductivity transmitter <sup>1</sup>	TB84	XX	X	0	0	0	X	X	X
<b>Input</b>									
Conductivity 4-electrode <sup>2</sup>		EC							
Conductivity 2-electrode <sup>2</sup>		TE							
Toroidal conductivity <sup>2</sup>		TC							
<b>Programming option</b>									
Basic			1						
Advanced <sup>3</sup>			2						
<b>Reserved</b>									
For future use				0					
<b>Reserved</b>									
For future use					0				
<b>Housing type</b>									
Anodized aluminum, powder coat polyester						0			
<b>Mounting hardware</b>									
None								0	
Pipe								1	
Hinge (for pipe or wall)								2	
Panel								3	
Wall								4	
<b>Agency approval</b>									
None									0
FM (Factory Mutual)									1
CSA (Canadian Standards Association)									2
<b>Tag</b>									
None									0
Stainless steel (4TB5003-0007)									1
Mylar™									2

### Notes.

- 1 One instruction manual included. Additional copy, part number OI/TB84TE-EN, OI/TB84EC-EN or OI/TB84TE-EN
- 2 Cable grip available separately, Part Number 4TB9515-0165
- 3 See product data sheets (DS/TB84TE-EN, DS/TB84EC-EN and DS/TB84TE-EN) for details of advanced programming options

## Installation accessories

Panel-mounting kit	4TB9515-0123
Pipe-mounting kit	4TB9515-0124
Hinge-mounting kit	4TB9515-0125
Wall-mounting kit	4TB9515-0156
Cable grip for ½ in hubs	4TB9515-0165
Cable grip for PG9 hubs	4TB9515-0191
Complete cable grip kit (2 each ½ in and 3 each PG9)	4TB9515-0198

## Acknowledgements

- Mylar is a registered trademark of Dupont Teijin Films

Sales



Service



---

**ABB Limited**

**Measurement & Analytics**

Oldends Lane, Stonehouse  
Gloucestershire, GL10 3TA  
UK

Tel: +44 (0)1453 826 661

Fax: +44 (0)1453 829 671

Email: [instrumentation@gb.abb.com](mailto:instrumentation@gb.abb.com)

**ABB Inc.**

**Measurement & Analytics**

125 E. County Line Road  
Warminster, PA 18974  
USA

Tel: +1 215 674 6000

Fax: +1 215 674 7183

**[abb.com/measurement](http://abb.com/measurement)**

---

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB.