


# 5SNG 0450R170390

## LoPak1 phase leg IGBT Module

$$V_{CE} = 1700 \text{ V}$$

$$I_C = 2 \times 450 \text{ A}$$

Press-fit pins for reliable auxiliary contacts  
 Ultra low-loss, rugged SPT++ chip-set  
 NTC thermistor for temperature sensing  
 Cu base-plate for low thermal resistance  
 Pre-Applied Thermal Interface Material (TIM) to improve thermal conductivity between module and heat sink  
 Industry standard package



### Maximum rated values <sup>1)</sup>

Parameter	Symbol	Conditions	min	max	Unit
Collector-emitter voltage	$V_{CES}$	$V_{GE} = 0 \text{ V}$ , $T_{vj} \geq 25 \text{ °C}$		1700	V
DC collector current	$I_C$	$T_C = 115 \text{ °C}$ , $T_{vj} = 175 \text{ °C}$		450	A
Peak collector current	$I_{CM}$	$t_p = 1 \text{ ms}$		900	A
Gate-emitter voltage	$V_{GES}$		-20	20	V
DC forward current	$I_F$			450	A
Peak forward current	$I_{FRM}$	$t_p = 1 \text{ ms}$		900	A
Surge current	$I_{FSM}$	$V_R = 0 \text{ V}$ , $T_{vj} = 175 \text{ °C}$ , $t_p = 10 \text{ ms}$ , half-sinewave		2250	A
IGBT short circuit SOA	$t_{psc}$	$V_{CC} = 1300 \text{ V}$ , $V_{CEM \text{ CHIP}} \leq 1700 \text{ V}$ $V_{GE} \leq 15 \text{ V}$ , $T_{vj} \leq 150 \text{ °C}$		10	$\mu\text{s}$
Isolation voltage	$V_{ISOL}$	1 min, $f = 50 \text{ Hz}$		4000	V
Junction temperature	$T_{vj}$		-40	175	$^{\circ}\text{C}$
Junction operating temperature	$T_{vj(op)}$		-40	175	$^{\circ}\text{C}$
Case temperature	$T_C$		-40	125 <sup>2)</sup> / 150	$^{\circ}\text{C}$
Storage temperature	$T_{stg}$		-40	125	$^{\circ}\text{C}$
Mounting torques <sup>3)</sup>	$M_s$	Base-heatsink, M5 screws	3	6	Nm
	$M_{t1}$	Main terminals, M6 screws	3	6	

<sup>1)</sup> Maximum rated values indicate limits beyond which damage to the device may occur per IEC 60747

<sup>2)</sup> For UL1557 compliance  $T_{Cmax}$  must be limited to 125 $^{\circ}\text{C}$

<sup>3)</sup> For detailed mounting instructions refer to ABB Document No. 5SYA 2113

**IGBT characteristic values <sup>4)</sup>**

Parameter	Symbol	Conditions	min	typ	max	Unit
Collector (-emitter) breakdown voltage	$V_{(BR)CES}$	$V_{GE} = 0\text{ V}$ , $I_C = 10\text{ mA}$ , $T_{vj} = 25\text{ °C}$	1700			V
Collector-emitter <sup>5)</sup> saturation voltage	$V_{CE\text{ sat}}$	$I_C = 450\text{ A}$ , $V_{GE} = 15\text{ V}$	$T_{vj} = 25\text{ °C}$	2.25	2.6	V
			$T_{vj} = 125\text{ °C}$	2.55		V
			$T_{vj} = 175\text{ °C}$	2.75		V
Collector cut-off current	$I_{CES}$	$V_{CE} = 1700\text{ V}$ , $V_{GE} = 0\text{ V}$	$T_{vj} = 25\text{ °C}$		0.1	mA
			$T_{vj} = 125\text{ °C}$		1.2	mA
			$T_{vj} = 175\text{ °C}$		20	mA
Gate leakage current	$I_{GES}$	$V_{CE} = 0\text{ V}$ , $V_{GE} = \pm 20\text{ V}$ , $T_{vj} = 175\text{ °C}$	-500		500	nA
Gate-emitter threshold voltage	$V_{GE(th)}$	$I_C = 12\text{ mA}$ , $V_{CE} = V_{GE}$ , $T_{vj} = 25\text{ °C}$	4.5		6.5	V
Gate charge	$Q_G$	$I_C = 450\text{ A}$ , $V_{CE} = 900\text{ V}$ , $V_{GE} = -15\text{ V} \dots 15\text{ V}$		3.2		$\mu\text{C}$
Input capacitance	$C_{ies}$	$V_{CE} = 25\text{ V}$ , $V_{GE} = 0\text{ V}$ , $f = 1\text{ MHz}$ , $T_{vj} = 25\text{ °C}$		28.8		nF
Internal gate resistance	$R_{Gint}$	per switch		1		$\Omega$
Turn-on delay time	$t_{d(on)}$	$V_{CC} = 900\text{ V}$ , $I_C = 450\text{ A}$ , $R_G = 0.47\ \Omega$ , $V_{GE} = \pm 15\text{ V}$ , $L_\sigma = 40\text{ nH}$ , inductive load	$T_{vj} = 25\text{ °C}$	245		ns
			$T_{vj} = 125\text{ °C}$	260		ns
			$T_{vj} = 175\text{ °C}$	270		ns
Rise time	$t_r$	$V_{CC} = 900\text{ V}$ , $I_C = 450\text{ A}$ , $R_G = 0.47\ \Omega$ , $V_{GE} = \pm 15\text{ V}$ , $L_\sigma = 40\text{ nH}$ , inductive load	$T_{vj} = 25\text{ °C}$	70		ns
			$T_{vj} = 125\text{ °C}$	90		ns
			$T_{vj} = 175\text{ °C}$	95		ns
Turn-off delay time	$t_{d(off)}$	$V_{CC} = 900\text{ V}$ , $I_C = 450\text{ A}$ , $R_G = 0.47\ \Omega$ , $V_{GE} = \pm 15\text{ V}$ , $L_\sigma = 40\text{ nH}$ , inductive load	$T_{vj} = 25\text{ °C}$	440		ns
			$T_{vj} = 125\text{ °C}$	540		ns
			$T_{vj} = 175\text{ °C}$	600		ns
Fall time	$t_f$	$V_{CC} = 900\text{ V}$ , $I_C = 450\text{ A}$ , $R_G = 0.47\ \Omega$ , $V_{GE} = \pm 15\text{ V}$ , $L_\sigma = 40\text{ nH}$ , inductive load	$T_{vj} = 25\text{ °C}$	110		ns
			$T_{vj} = 125\text{ °C}$	160		ns
			$T_{vj} = 175\text{ °C}$	165		ns
Turn-on switching energy	$E_{on}$	$V_{CC} = 900\text{ V}$ , $I_C = 450\text{ A}$ , $R_G = 0.47\ \Omega$ , $V_{GE} = \pm 15\text{ V}$ , $L_\sigma = 40\text{ nH}$ , inductive load	$T_{vj} = 25\text{ °C}$	95		mJ
			$T_{vj} = 125\text{ °C}$	145		mJ
			$T_{vj} = 175\text{ °C}$	185		mJ
Turn-off switching energy	$E_{off}$	$V_{CC} = 900\text{ V}$ , $I_C = 450\text{ A}$ , $R_G = 0.47\ \Omega$ , $V_{GE} = \pm 15\text{ V}$ , $L_\sigma = 40\text{ nH}$ , inductive load	$T_{vj} = 25\text{ °C}$	90		mJ
			$T_{vj} = 125\text{ °C}$	135		mJ
			$T_{vj} = 175\text{ °C}$	165		mJ
Short circuit current	$I_{SC}$	$t_{psc} \leq 10\ \mu\text{s}$ , $V_{GE} = 15\text{ V}$ , $V_{CC} = 1300\text{ V}$ , $V_{CEM\text{ CHIP}} \leq 1700\text{ V}$	$T_{vj} = 150\text{ °C}$	1500		A

<sup>4)</sup> Characteristic values according to IEC 60747 - 9

<sup>5)</sup> Collector-emitter saturation voltage is given at chip level

## Diode characteristic values <sup>6)</sup>

Parameter	Symbol	Conditions	min	typ	max	Unit
Forward voltage <sup>7)</sup>	V <sub>F</sub>	I <sub>F</sub> = 450 A	T <sub>vj</sub> = 25 °C	1.6	2.2	V
			T <sub>vj</sub> = 125 °C		1.75	V
			T <sub>vj</sub> = 175 °C		1.7	V
Peak reverse recovery current	I <sub>RM</sub>		T <sub>vj</sub> = 25 °C	480		A
			T <sub>vj</sub> = 125 °C		490	A
			T <sub>vj</sub> = 175 °C		530	A
Recovered charge	Q <sub>r</sub>	V <sub>CC</sub> = 900 V, I <sub>F</sub> = 450 A, V <sub>GE</sub> = ±15 V, R <sub>G</sub> = 0.47 Ω, di/dt = 5.3 kA/μs L <sub>σ</sub> = 40 nH, inductive load	T <sub>vj</sub> = 25 °C	120		μC
			T <sub>vj</sub> = 125 °C		190	μC
			T <sub>vj</sub> = 175 °C		260	μC
Reverse recovery time	t <sub>rr</sub>		T <sub>vj</sub> = 25 °C	490		ns
			T <sub>vj</sub> = 125 °C		790	ns
			T <sub>vj</sub> = 175 °C		930	ns
Reverse recovery energy	E <sub>rec</sub>		T <sub>vj</sub> = 25 °C	75		mJ
			T <sub>vj</sub> = 125 °C		115	mJ
			T <sub>vj</sub> = 175 °C		155	mJ

<sup>6)</sup> Characteristic values according to IEC 60747 - 2

<sup>7)</sup> Forward voltage is given at chip level

## NTC Thermistor

Parameter	Symbol	Conditions	min	typ	max	Unit
Rated resistance	R <sub>25</sub>	T <sub>C</sub> = 25 °C		5		kΩ
R100	R <sub>100</sub>	T <sub>C</sub> = 100 °C	468		517	Ω
B-value	B <sub>25/50</sub>	R <sub>25</sub> = R <sub>25</sub> exp [B <sub>25/50</sub> (1/T <sub>2</sub> - 1/(298.15K))]		3375		K
B-value	B <sub>25/100</sub>	R <sub>25</sub> = R <sub>25</sub> exp [B <sub>25/100</sub> (1/T <sub>2</sub> - 1/(298.15K))]		3433		K

## Package properties <sup>8)</sup>

Parameter	Symbol	Conditions	min	typ	max	Unit
IGBT thermal resistance junction to case	R <sub>th(j-c)IGBT</sub>	per switch			0.048	K/W
Diode thermal resistance junction to case	R <sub>th(j-c)DIODE</sub>				0.087	K/W
IGBT thermal resistance <sup>3)</sup> case to heatsink	R <sub>th(c-s)IGBT</sub>	IGBT per switch, λ grease = 5.2W/m x K		0.025		K/W
Diode thermal resistance <sup>3)</sup> case to heatsink	R <sub>th(c-s)DIODE</sub>	Diode per switch, λ grease = 5.2W/m x K		0.041		K/W
Comparative tracking index	CTI		200			
Module stray inductance	L <sub>σ CE</sub>	per switch		25		nH
Resistance, terminal-chip	R <sub>CC'+EE'</sub>	per switch	T <sub>C</sub> = 25 °C	0.95		mΩ
			T <sub>C</sub> = 125 °C	1.35		
			T <sub>C</sub> = 175 °C	1.55		


<sup>3)</sup> For detailed mounting instructions refer to ABB Document No. 5SYA 2113

## Mechanical properties <sup>8)</sup>


Parameter	Symbol	Conditions	min	typ	max	Unit
Dimensions	L x W x H	Typical		152 x 62 x 17		mm
Clearance distance in air	d <sub>a</sub>	according to IEC 60664-1 and EN 50124-1	Term. to base:	12.5		mm
			Term. to term:	10		
Surface creepage distance	d <sub>s</sub>	according to IEC 60664-1 and EN 50124-1	Term. to base:	14.5		mm
			Term. to term:	13		
Mass	m			350		g

<sup>8)</sup> Package and mechanical properties according to IEC 60747 - 15


## Electrical configuration



## Outline drawing <sup>3)</sup>



### PCB drill hole pattern for press-fit



#### Note:

Ø1<sup>+0.09</sup><sub>-0.06</sub> Diameter of finished plated through-hole

Ø1.15 Diameter of drilled hole

Note: all dimensions are shown in millimeters

<sup>3)</sup> For detailed mounting instructions refer to ABB Document No. 5SYA 2113

This is an electrostatic sensitive device, please observe the international standard IEC 60747-1, chap. VIII.  
 This product has been designed and qualified for Industrial Level.




Fig. 1 Typical on-state characteristics, chip level




Fig. 2 Typical transfer characteristics, chip level




Fig. 3 Typical output characteristics, chip level




Fig. 4 Typical output characteristics, chip level




Fig. 5 Typical switching energies per pulse vs. collector current




Fig. 6 Typical switching energies per pulse vs. gate resistor




Fig. 7 Typical switching times vs. collector current




Fig. 8 Typical switching times vs. gate resistor




Fig. 9 Typical gate charge characteristics




Fig. 10 Turn-off safe operating area (RBSOA)




Fig. 11 Typical reverse recovery characteristics vs. forward current




Fig. 12 Typical reverse recovery characteristics vs.  $di/dt$




Fig. 13 Typical diode forward characteristics chip level




Fig. 14 Safe operating area diode (SOA)




Fig. 15 Thermal impedance vs. time

Analytical function for transient thermal impedance:

$$Z_{th(j-c)}(t) = \sum_{i=1}^n R_i (1 - e^{-t/\tau_i})$$

	i	1	2	3	4	5
IGBT	R <sub>i</sub> (K/kW)	4.97	33.5	6.07	3.29	
	τ <sub>i</sub> (ms)	1.43	42	318	2400	
DIODE	R <sub>i</sub> (K/kW)	11.7	58.9	11.9	3.99	
	τ <sub>i</sub> (ms)	1.87	42.8	262	2290	



**Related documents:**

5SYA 2045 Thermal runaway during blocking  
5SYA 2053 Applying IGBT  
5SYA 2058 Surge currents for IGBT diodes  
5SYA 2093 Thermal design and temperature ratings of IGBT modules  
5SYA 2098 Paralleling of IGBT modules  
5SYA 2113 Mounting instructions for LoPak1 modules

ABB Power Grids Switzerland Ltd, Semiconductors  
A Hitachi ABB Joint Venture  
Fabrikstrasse 3  
CH-5600 Lenzburg  
Switzerland

Phone: +41 58 586 1419  
Fax: +41 58 586 1306  
E-Mail: [abbsem@hitachi-powergrids.com](mailto:abbsem@hitachi-powergrids.com)  
Internet: [www.hitachi-powergrids.com/semiconductors](http://www.hitachi-powergrids.com/semiconductors)

We reserve the right to make technical changes or to modify the contents of this document without prior notice.

We reserve all rights in this document and the information contained therein. Any reproduction or utilization of this document or parts thereof for commercial purposes without our prior written consent is forbidden.

Any liability for use of our products contrary to the instructions in this document is excluded.