



On-load tap-changer type UCGL./III, VUCGL./III, UCLL./III, UC DL./III, 19 tap positions, linear switching.
 Max. effective No. of turns in pos. 1.
 The tap-changer is delivered set in pos. 10,
 the preceding pos. was 9.

Lindningskopplare typ UCGL./III, VUCGL./III, UCLL./III, UC DL./III, 19 lägen, linjär koppling.
 Max. antal effektiva varv i läge 1.
 Lindningskopplaren levereras inställd i läge 10,
 föregående läge var 9.



Pos.	Tap selector and diverter switch connect
Läge	Väljaren och lastkopplaren förbinder
1	1-V-x
2	2-H-v
3	3-V-x
4	4-H-v
5	5-V-x
6	6-H-v
7	7-V-x
8	8-H-v
9	9-V-x
10	10-H-v
11	11-V-x
12	12-H-v
13	13-V-x
14	14-H-v
15	15-V-x
16	16-H-v
17	17-V-x
18	18-H-v
19	19-V-x

30

We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden. © ABB 19

The tap-changer is shown in pos. 10,
 the preceding pos. was 9.
 The tap selector is seen from above.
 Contact arm V is located above contact arm H.

Lindningskopplaren visad i läge 10,
 föregående läge var 9.
 Väljaren sedd uppifrån.
 Kontaktarm V ligger över kontaktarm H.

Continuous lines show leads included in the tap-changer. Dashed lines show leads belonging to the cleats and leads.

Heldragna linjer visar ledare som ingår i lindningskopplaren. Streckade linjer visar ledare som tillhör anslutningsdonet.

Drawn by Form No.	Sheet	Year	Week	Cont
	Dept	Rev Ind	Revision	Appd
	Rev Ind	Revision	Appd	Year
	Rev Ind	Revision	Appd	Year
Design checked by	Accepted by qual control	Accepted for prod by	Description (English) CONNECTION DIAGRAM	
	Design checked by G.Andersson GA	Drawn by T.Larsen	Description (own language) KOPPLINGSSHEMA	
Design checked by	Drawing checked by A.Hultberg M	Issued by Dept Year Week COM/FOK 07 49	File name 0367-15	
	Asea Brown Boveri		Lang	Sheet
Rev Ind			Cont	

5492 0367-15