



Test Report				Date of issue: 16.3.2015							
Customer:				Serial No.:							
Customer ref.:				Order No.:							
				Type: M3GP 200MLA 6							
				Product Code: 3GGP203410-ADL							
				Protection type: Ex nA IIC T3 Gc							
				Cert. No.: LCIE 13 ATEX 1034 X/							
				IECEX LCIE 13.0047 X							
Rating:											
				V	Hz	kW	r/min	A	cos φ	Duty	
3-Motor				690	Y	50	18,5	989	21,6	0,82	S1
Insul.cl.F				400	D	50	18,5	989	35,2	0,82	S1
IP55				415	D	50	18,5	990	34,5	0,81	S1
				440	D	60	18,5	1189	31,7	0,83	S1
Eff class IE3				460	D	60	18,5	1190	30,6	0,82	S1
				50Hz: IE3-91,7%(100%)-91,9%(75%)-91,2%(50%)							
				60Hz: IE3-93,0%(100%)							
Resistance				Insulation resistance at 80 °C				Overload			
Line				2000 MΩ 1000 V				Torque 160% 15s			
U ₁ - V ₁				Ambient: 26 °C				Speed 120% 120s			
0,28990 Ω								Current 150% 15s			
U ₁ - W ₁				0,28910 Ω							
V ₁ - W ₁				0,28910 Ω							
				High-voltage test winding 1900 V				60 s			
Test	Torque [Nm]	Line U[V]	f[Hz]	Input I[A]	P1 [kW]	Output P2 [kW]	η[r/min]	cos φ	η [%]		
No load test		400,7 D	50	13,6	0,60		998	0,06			
Locked rotor test		85,3 D	50	35,1	1,73		0	0,33			
Thermal test (100% load)	178,7	400,4 D	50	35,2	20,1	18,5	989	0,82	92,0		
Partial load points:											
~75% load	134,3	400,1 D	50	27,9	15,1	13,9	991	0,78	92,2		
~50% load	89,6	400,9 D	50	21,3	10,1	9,3	995	0,68	91,6		
~25% load	44,8	400,9 D	50	16,3	5,3	4,6	997	0,47	87,4		
Temperature rise at rated load.				[°C]	[K]	Method	Measurement method				
Stator winding :				48	1		1 Resistance				
Frame :				28	2		2 Thermocouples				
Bearing D-end :				31	2		3 Thermometer				
Rotor:				60	3						
Ambient Temperature :				25	2						
These tests have been carried out on motor no. 3G1P141700184, on date 2014-07-07 which is identical in design with the above.											
Manufactured and tested in accordance with rules of IEC 60034-1 and IEC 60034-2-1. PLL determined from residual loss.											
On behalf of customer											
On behalf of manufacturer Date of test											
Tested by ABB Oy, Motors and Generators, Vaasa, Finland											
Telephone +358 10 2211											
Telefax +358 10 22 47372											

Computer print-out valid without signature.