


# MULTIPLES OF CURRENT RATING (In)



## Time Current Curve

Available Ratings (Amperes)

Type	Model	Trip Unit	Frame Amps	Current Rating (In)
MCCB	XT5	Ekip Touch/Hi-Touch	400/600	250 400 300 600

Voltage Rating: 600Vac, 50 to 60 hz systems

electrification.us.abb.com

## Molded Case Circuit Breaker

### Type Tmax XT5 with Ekip Touch/Hi-Touch LSI/LSIG Long Time Curve: I2T

**Operating Conditions:** Curves apply at 50 to 60 Hertz and ambient temperature from -25°C to +70°C up to an altitude of 2000 meters. Electronic trip units do not undergo any variations in performance as the temperature varies, but, in the case of temperatures exceeding +40°C, the maximum setting for protection L (protection against overloads) must be reduced, as indicated in the UL Catalog.

**Reduced Energy Let Through (RELT):** is adjusted by engaging and setting the second instantaneous function (2I-50). The setting range and increments are identical to the primary instantaneous (I-50).

**Instantaneous Override:** When instantaneous protection is turned off, the breaker will immediately trip for any current that is equal to or greater than **8,000A** minus 15.62% or plus 25.0%

**Additional Long Time Curve Options:** Refer to the following TCCs for other long time delay curve types.  
**SI** (Short Inverse): 9AKK108468A0819  
**VI** (Very Inverse): 9AKK108468A0818  
**EI** (Extremely Inverse): 9AKK108468A0817  
**I4T** (Fuse Response): 9AKK108468A0816  
**Ground Fault:** 9AKK108468A0815