



中国国家强制性产品认证证书

证书编号: 2024010302658032

认证委托人名称及地址

ABB Oy

Muottitie 2A FI-65320 VAASA, Finland

生产者名称及地址

ABB Oy

Muottitie 2A FI-65320 VAASA, Finland

生产企业名称及地址

ABB Oy

Muottitie 2A FI-65320 VAASA, Finland

产品名称和系列、型号、规格

隔离开关

OT315, OT400: Uimp: 12kV;Ui: 1000V;Ith: 315A(OT315),400A(OT400);Ue:
500V/690V;Ie:315A(OT315),400A(OT400);Icm(峰值): 65kA;Icw: 15kA/1s,
31kA/0.15s;Iq:100kA/500V,80kA/690V;使用类别: AC-21A, AC-22A, AC-23A;极数: 3P, 4P;适用频
率: 50/60Hz;IP20(仅对前面板); 型号解释见附页

产品标准和技术要求

GB/T 14048.3-2017

上述产品符合《强制性产品认证实施规则 低压电器 低压元器件》
(CNCA-C03-02:2024)的要求, 特发此证。

发证日期: 2024年07月15日 有效期至: 2029年07月14日

证书信息和有效性可扫描下方二维码或登录发证机构网站查验,
也可在认监委网站 (www.cnca.gov.cn) 查询。



签发:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司





中国国家强制性产品认证证书

证书编号: 2024010302658032

证书附页: 第 1 页 共 1 页

型号解释:

OT	315	E	13	W	H	P
						P = handle & shaft included 带门上安装手柄和轴 K = direct handle 带直接安装手柄 Blank = without handle & shaft 不带手柄和轴
						H = silver layer 20μ 镀银 20μ Blank = silver layer 7μ 镀银 7μ
						W=insulation plates between poles 极间带绝缘板
						Poles (according to side of mechanism) 极数 3 poles (3 极) - 12, 21, 03, 30 4 poles (4 极)- 13, 31, 22, 04, 40 1. number = number of poles on left side 第一位数字表示在机械结构左边的极数 2. number = number of poles in right side 第一位数字表示在机械结构左边的极数
						Structure 操作方式 E = front operated, used in IEC types E = 正面操作-IEC 标准 ES=side operated, used in IEC types ES = 侧面操作-IEC 标准 U = front operated, used in IEC & UL types U = 正面操作-IEC&UL 标准 US = side operated, used in IEC & UL types US = 侧面操作-IEC&UL 标准
						Switch size 电流等级(A) 315, 400
						Switch disconnector 隔离开关型号

本页为证书附页，应与证书主页同时使用。



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO.: 2024010302658032

NAME AND ADDRESS OF THE APPLICANT

ABB Oy
Muottitie 2A FI-65320 VAASA, Finland

NAME AND ADDRESS OF THE MANUFACTURER

ABB Oy
Muottitie 2A FI-65320 VAASA, Finland

NAME AND LOCATION OF THE FACTORY

ABB Oy
Muottitie 2A FI-65320 VAASA, Finland

PRODUCT NAME,MODEL AND SPECIFICATION

SWITCH-DISCONNECTORS

OT315, OT400 : Uimp: 12kV;Ui: 1000V;Ith: 315A(OT315),400A(OT400);Ue:
500V/690V;Ie:315A(OT315),400A(OT400);Icm(Peak): 65kA;Icw: 15kA/1s,
31kA/0.15s;Iq:100kA/500V,80kA/690V;Utilization Category: AC-21A, AC-22A, AC-23A;Poles: 3P, 4P;Applicable
frequency: 50/60Hz;IP20(only for front panels) ; See the appendix

STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 14048.3-2017

This is to certify that the above mentioned product(s) complies with the requirements of
implementation rules for compulsory certification(REFNO. CNCA-C03-02:2024).

Valid from: Jul.15,2024

Valid until: Jul.14,2029

The certificate information and validity could be checked by scanning the QR code below or logging in to
the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).



SIGNATURE:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.





Appendix: Page 1 of 1

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

OT	315	E	13	W	H	P	
							P = handle & shaft included 带门上安装手柄和轴 K = direct handle 带直接安装手柄 Blank = without handle & shaft 不带手柄和轴
							H = silver layer 20μ 镀银 20μ Blank = silver layer 7μ 镀银 7μ
							W=insulation plates between poles 极间带绝缘板
							Poles (according to side of mechanism) 极数 3 poles (3 极) - 12, 21, 03, 30 4 poles (4 极)- 13, 31, 22, 04, 40 1. number = number of poles on left side 第一位数字表示在机械结构左边的极数 2. number = number of poles in right side 第一位数字表示在机械结构右边的极数
							Structure 操作方式 E = front operated, used in IEC types E = 正面操作-IEC 标准 ES=side operated, used in IEC types ES = 侧面操作-IEC 标准 U = front operated, used in IEC & UL types U = 正面操作-IEC&UL 标准 US = side operated, used in IEC & UL types US = 侧面操作-IEC&UL 标准
							Switch size 电流等级(A) 315, 400
							Switch disconnector 隔离开关型号

This page is attached to the certificate and should be used at the same time as the certificate page.



CHINA QUALITY CERTIFICATION CENTRE CO., LTD.