



Test Report				Date of issue: 4.6.2014						
				Serial No.: 3GP11020934						
				Type: M3JP 315SMC 6 B3						
				Product Code: 3GJP313230-ADG						
				Protection type: Ex d IIB T4 Gb						
				Cert. No.: LCIE 11 ATEX 3090X / IECEx LCI 04.0007X						
Rating:										
		V	Hz	kW	r/min	A	cos φ	Duty		
3-Motor		400	D 50	110	991	201	0,83	S1		
Insul.cl.F		415	D 50	110	992	196	0,82	S1		
IP55		690	Y 50	110	991	117	0,83	S1		
Eff class IE2		400 V 50Hz : IE2 - 95.0(100%) - 95.0(75%) - 94,6(50%)								
Resistance Line				Ambient: 20,0 °C			Insulation resistance at 47,5 °C		Overload	
U ₁ - V ₁				0,02490 Ω			14000 MΩ		1000 V	
U ₁ - W ₁				0,02488 Ω					Torque 160 % 15s	
V ₁ - W ₁				0,02491 Ω						
				High-voltage test winding			1900 V		60 s	
Test	Torque [Nm]	Line U[V]	f[Hz]	Input I[A]	P1 [kW]	Output P2 [kW]	n[r/min]	cos φ	η [%]	
No load test		399,9 D	50	74,8	2,30		1000	0,04		
Locked rotor test		76,8 D	50	202,0	8,16		0	0,30		
Thermal test (100% load)	1060,0	400,3 D	50	202,1	116,1	110,0	992	0,83	94,8	
Partial load points:										
~75% load	795,7	400,1 D	50	158,6	86,9	82,5	994	0,79	95,0	
~50% load	529,0	400,2 D	50	119,7	58,2	55,0	996	0,70	94,5	
~25% load	264,0	400,1 D	50	88,9	30,1	27,5	998	0,49	91,5	
Temperature rise at rated load.				°C	[K]	Method		Measurement method		
Stator winding :				57,7	1	1 Resistance				
Frame :				33,5	2	2 Thermometer				
Bearing D-end :				48,3	2	3 Thermocouples				
Ambient Temperature :				25,0	2					
Manufactured and tested in accordance with rules of IEC 60034-1 and IEC 60034-2-1. PLL determined from residual loss.										
On behalf of customer										
On behalf of manufacturer		Date of test		26.10.2011						
Tested by ABB Oy, Motors and Generators, Vaasa, Finland						Telephone +358 10 2211		Telefax +358 10 22 47372		

Computer print-out valid without signature.

ABB, Motors and Generators
www.abb.com/motors&generators