



中国国家强制性产品认证证书

证书编号：2024010307644548

认证委托人名称及地址

ABB Stotz-Kontakt GmbH
Eppelheimer Strasse 82 69123 Heidelberg Germany

生产者名称及地址

ABB Stotz-Kontakt GmbH
Eppelheimer Strasse 82 69123 Heidelberg Germany

生产企业名称及地址

北京 ABB 低压电器有限公司
北京市北京经济技术开发区康定街 17 号

产品名称和系列、型号、规格

微型断路器

S201,S201-NA,S202,S203,S203-NA,S204 详情见附页

产品标准和技术要求

GB/T 10963.1-2020

上述产品符合《强制性产品认证实施规则 低压电器 低压元器件》
(CNCA-C03-02:2024) 的要求，特发此证。

发证日期：2024 年 09 月 02 日 有效期至：2029 年 06 月 18 日

本证书为变更证书，证书首次颁发日期：2024 年 06 月 19 日
证书信息和有效性可扫描下方二维码或登录发证机构网站查验，
也可在认监委网站（www.cnca.gov.cn）查询。



签发：

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司





中国国家强制性产品认证证书

证书编号: 2024010307644548

证书附页: 第 1 页 共 1 页

规格型号: S201, S201-NA, S202, S203, S203-NA, S204

额定冲击耐受电压 U_{imp} : 4kV

额定绝缘电压 U_i : 250VAC (1P, 1P+N) (相对零), 500VAC (1P, 2P, 3P, 4P, 3P+N) (相对相)

额定工作电压 U_e : AC 230V (1P+N), AC 230/400V (1P), AC400V (2P, 3P, 3P+N, 4P)

额定电流 I_n : B: 1A, 2A, 3A, 4A, 6A, 8A, 10A, 13A, 16A, 20A, 25A, 32A, 40A, 50A, 63A

C: 0.5A, 1A, 1.6A, 2A, 3A, 4A, 6A, 8A, 10A, 13A, 16A, 20A, 25A, 32A, 40A, 50A, 63A

D: 0.5A, 1A, 1.6A, 2A, 3A, 4A, 6A, 8A, 10A, 13A, 16A, 20A, 25A, 32A, 40A, 50A, 63A

瞬时脱扣类型: B, C, D 型

运行短路能力 I_{cs} : 6000A

额定短路能力 I_{cn} : 6000A

极数: 1P, 1P+N(带一个保护极, N 极可开闭), 2P, 3P, 3P+N(带三个保护极, N 极可开闭), 4P

型号的解释:

S20 **1** - **NA** **C** **16**
1 2 3 4 5

1——产品系列

2——极数: 1-1P, 2-2P, 3-3P, 4-4P

3——中性极: 空白为无中性极, -NA 为带有中性极

4——瞬时脱扣特性: B-B 特性; C-C 特性; D-D 特性

5——额定电流: B: 1A; 2A; 3A; 4A; 6A; 8A; 10A; 13A; 16A; 20A; 25A; 32A; 40A; 50A; 63A;

C: 0.5A; 1A; 1.6A; 2A; 3A; 4A; 6A; 8A; 10A; 13A; 16A; 20A; 25A; 32A; 40A; 50A; 63A;

D: 0.5A; 1A; 1.6A; 2A; 3A; 4A; 6A; 8A; 10A; 13A; 16A; 20A; 25A; 32A; 40A; 50A; 63。

本页为证书附页, 应与证书主页同时使用。



中国质量认证中心

CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO.: 2024010307644548

NAME AND ADDRESS OF THE APPLICANT

ABB Stotz-Kontakt GmbH
Eppelheimer Strasse 82 69123 Heidelberg Germany

NAME AND ADDRESS OF THE MANUFACTURER

ABB Stotz-Kontakt GmbH
Eppelheimer Strasse 82 69123 Heidelberg Germany

NAME AND LOCATION OF THE FACTORY

ABB LV Installation Materials Co., Ltd. Beijing
No.17 Kangding Street, Beijing Economic-Technological Development Area 100176, P.R. China

PRODUCT NAME, MODEL AND SPECIFICATION

Miniature Circuit-breaker
S201, S201-NA, S202, S203, S203-NA, S204 see the attachment

STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 10963.1-2020

This is to certify that the above mentioned product(s) complies with the requirements of
implementation rules for compulsory certification (REFNO. CNCA-C03-02:2024).

Valid from: Sep.02,2024

Valid until: Jun.18,2029

Date of original issued: Jun.19,2024

The certificate information and validity could be checked by scanning the QR code below or logging in to
the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).



SIGNATURE:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO. : 2024010307644548

Appendix: Page 1 of 1

S201,S201-NA,S202,S203,S203-NA,S204

Uimp : 4kV Ui : 250VAC(1P,1P+N) (Relative zero) , 500VAC(1P,2P,3P,4P,3P+N)

(phase-to-phase)

Ue : AC 230V (1P+N),AC 230/400V(1P), AC400V (2P,3P,3P+N,4P)

In : B: 1A,2A,3A,4A,6A, 8A,10A,13A,16A,20A,25A,32A,40A, 50A, 63A

C: 0.5A,1A,1.6A,2A,3A,4A,6A,8A,10A,13A,16A,20A,25A,32A,40A,50A,63A

D: 0.5A,1A,1.6A,2A,3A,4A,6A,8A,10A,13A,16A,20A,25A,32A,40A,50A,63A

instantaneous tripping type : B , C , D 型 Ics : 6000A; Icn : 6000A

pole : 1P, 1P+N(1 protected poles with a switched neutral pole) ,2P , 3P , 3P+N(3

protected poles with a switched neutral pole), 4P

explanation :

S20 **1** - **NA** **C** **16**
1 **2** **3** **4** **5**

1——产品系列

2——极数: 1-1P, 2-2P, 3-3P, 4-4P

3——中性极: 空白为无中性极, -NA 为带有中性极

4——瞬时脱扣特性: B-B 特性; C-C 特性; D-D 特性

5——额定电流:B: 1A; 2A; 3A; 4A; 6A; 8A;10A; 13A; 16A; 20A; 25A; 32A; 40A, 50A, 63A;

C: 0.5A; 1A; 1.6A; 2A; 3A; 4A; 6A; 8A; 10A; 13A; 16A; 20A; 25A; 32A; 40A, 50A, 63A;

D: 0.5A; 1A; 1.6A; 2A; 3A; 4A; 6A; 8A; 10A; 13A; 16A; 20A; 25A; 32A; 40A, 50A, 63.

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.