

# Stanilite®

## Platinum exit LED Quickfit® vandal resistant



Catalogue no.	Description
<b>EM products</b>	
VPQLEDP	Platinum exit LED Quickfit vandal resistant pictograph
<b>Spare parts</b>	
03-01302P	Battery LiFePO4 3.2V 3.2Ah
PQFLEDP-FR	Platinum exit LED Quickfit frame only

### Range

Platinum range


### Product group

Exit LED



### Features

- LED technology 100,000 hours plus lamp life
- Low power consumption and LED light source for reduced operation and maintenance costs
- IK09 mechanical impact resistance
- Vermin resistance
- Advanced charging technology combined with Lithium iron phosphate battery for long life and low maintenance
- Unique internal steel slide connect bracket for quick installation and easy maintenance
- Strong steel body and end cap
- Anti-tamper cover screws
- Universal wall/ceiling mounting
- Includes all pictograph diffuser options for single or double sided installation



Dimensions		
Length	Width	Height
410mm	140mm	265mm
Weight		
Model	Weight	
EM	7.8kg	
Construction		
Part	Construction	
Body and end cap	Steel body and end cap with anti-tamper cover screws White powder coated finish	
Diffuser	Extra tough UV stabilised polycarbonate	

<b>Light source</b>			
	<b>Model</b>	<b>Light source</b>	
	EM	Multiple LED 1.6W	

<b>Power consumption</b>			
	<b>Model</b>	<b>Power consumption</b>	
	EM	3.2W	

Note: Preliminary results

<b>Photometrics</b>			
	<b>Model</b>	<b>Class</b>	<b>Classification</b>
	EM	C0	E1.25
		C90	E1.25

Note: Preliminary results

Note:

- Designed to comply with AS2293 and meet relevant Australian EMC standards