

# 5SNG 0250P330305

## HiPak IGBT Module

$V_{CE} = 3300 \text{ V}$   
 $I_C = 250 \text{ A}$

Ultra low-loss, rugged SPT+ chip-set  
 Smooth switching SPT+ chip-set for good EMC  
 AlSiC base-plate for high power cycling capability  
 AlN substrate for low thermal resistance  
 Recognized under UL1557, File E196689



### Maximum rated values <sup>1)</sup>

Parameter	Symbol	Conditions	min	max	Unit
Collector-emitter voltage	$V_{CES}$	$V_{GE} = 0 \text{ V}$ , $T_{vj} \geq 25 \text{ }^\circ\text{C}$		3300	V
DC collector current	$I_C$	$T_C = 100 \text{ }^\circ\text{C}$ , $T_{vj} = 150 \text{ }^\circ\text{C}$		250	A
Peak collector current	$I_{CM}$	$t_p = 1 \text{ ms}$		500	A
Gate-emitter voltage	$V_{GES}$		-20	20	V
Total power dissipation	$P_{tot}$	$T_C = 25 \text{ }^\circ\text{C}$ , $T_{vj} = 150 \text{ }^\circ\text{C}$		2450	W
DC forward current	$I_F$			250	A
Peak forward current	$I_{FRM}$	$t_p = 1 \text{ ms}$		500	A
Surge current	$I_{FSM}$	$V_R = 0 \text{ V}$ , $T_{vj} = 150 \text{ }^\circ\text{C}$ , $t_p = 10 \text{ ms}$ , half-sinewave		2250	A
IGBT short circuit SOA	$t_{psc}$	$V_{CC} = 2500 \text{ V}$ , $V_{CEM \text{ CHIP}} \leq 3300 \text{ V}$ $V_{GE} \leq 15 \text{ V}$ , $T_{vj} \leq 150 \text{ }^\circ\text{C}$		10	$\mu\text{s}$
Isolation voltage	$V_{isol}$	1 min, $f = 50 \text{ Hz}$		6000	V
Junction temperature	$T_{vj}$			175	$^\circ\text{C}$
Junction operating temperature	$T_{vj(op)}$		-50	150	$^\circ\text{C}$
Case temperature	$T_C$		-50	125	$^\circ\text{C}$
Storage temperature	$T_{stg}$		-50	125	$^\circ\text{C}$
Mounting torques <sup>2)</sup>	$M_s$	Base-heatsink, M6 screws	4	6	Nm
	$M_{t1}$	Main terminals, M6 screws	4	6	

<sup>1)</sup> Maximum rated values indicate limits beyond which damage to the device may occur per IEC 60747

<sup>2)</sup> For detailed mounting instructions refer to ABB Document No. 5SYA 2039

### IGBT characteristic values <sup>3)</sup>

Parameter	Symbol	Conditions	min	typ	max	Unit
Collector (-emitter) breakdown voltage	$V_{(BR)CES}$	$V_{GE} = 0 \text{ V}$ , $I_C = 10 \text{ mA}$ , $T_{vj} = 25 \text{ °C}$	3300			V
Collector-emitter <sup>4)</sup> saturation voltage	$V_{CE \text{ sat}}$	$I_C = 250 \text{ A}$ , $V_{GE} = 15 \text{ V}$	$T_{vj} = 25 \text{ °C}$	2.5	2.9	V
			$T_{vj} = 125 \text{ °C}$	3.1	3.4	V
			$T_{vj} = 150 \text{ °C}$	3.25		V
Collector cut-off current	$I_{CES}$	$V_{CE} = 3300 \text{ V}$ , $V_{GE} = 0 \text{ V}$	$T_{vj} = 25 \text{ °C}$		0.17	mA
			$T_{vj} = 125 \text{ °C}$	3.5	7	mA
			$T_{vj} = 150 \text{ °C}$	17		mA
Gate leakage current	$I_{GES}$	$V_{CE} = 0 \text{ V}$ , $V_{GE} = \pm 20 \text{ V}$ , $T_{vj} = 125 \text{ °C}$	-500		500	nA
Gate-emitter threshold voltage	$V_{GE(TO)}$	$I_C = 40 \text{ mA}$ , $V_{CE} = V_{GE}$ , $T_{vj} = 25 \text{ °C}$	5		7	V
Gate charge	$Q_{ge}$	$I_C = 250 \text{ A}$ , $V_{CE} = 1800 \text{ V}$ , $V_{GE} = -15 \text{ V} \dots 15 \text{ V}$		1.8		$\mu\text{C}$
Input capacitance	$C_{ies}$	$V_{CE} = 25 \text{ V}$ , $V_{GE} = 0 \text{ V}$ , $f = 1 \text{ MHz}$ , $T_{vj} = 25 \text{ °C}$		25.2		nF
Output capacitance	$C_{oes}$			2.1		nF
Reverse transfer capacitance	$C_{res}$			0.64		nF
Turn-on delay time	$t_{d(on)}$	$V_{CC} = 1800 \text{ V}$ , $I_C = 250 \text{ A}$ , $R_G = 10 \text{ }\Omega$ , $C_{GE} = 0 \text{ nF}$ , $V_{GE} = \pm 15 \text{ V}$ , $L_\sigma = 400 \text{ nH}$ , inductive load	$T_{vj} = 25 \text{ °C}$	445		ns
			$T_{vj} = 125 \text{ °C}$	450		ns
			$T_{vj} = 150 \text{ °C}$	455		ns
Rise time	$t_r$	$V_{CC} = 1800 \text{ V}$ , $I_C = 250 \text{ A}$ , $R_G = 10 \text{ }\Omega$ , $C_{GE} = 0 \text{ nF}$ , $V_{GE} = \pm 15 \text{ V}$ , $L_\sigma = 400 \text{ nH}$ , inductive load	$T_{vj} = 25 \text{ °C}$	195		ns
			$T_{vj} = 125 \text{ °C}$	200		ns
			$T_{vj} = 150 \text{ °C}$	210		ns
Turn-off delay time	$t_{d(off)}$	$V_{CC} = 1800 \text{ V}$ , $I_C = 250 \text{ A}$ , $R_G = 10 \text{ }\Omega$ , $C_{GE} = 0 \text{ nF}$ , $V_{GE} = \pm 15 \text{ V}$ , $L_\sigma = 400 \text{ nH}$ , inductive load	$T_{vj} = 25 \text{ °C}$	1160		ns
			$T_{vj} = 125 \text{ °C}$	1330		ns
			$T_{vj} = 150 \text{ °C}$	1370		ns
Fall time	$t_f$	$V_{CC} = 1800 \text{ V}$ , $I_C = 250 \text{ A}$ , $R_G = 10 \text{ }\Omega$ , $C_{GE} = 0 \text{ nF}$ , $V_{GE} = \pm 15 \text{ V}$ , $L_\sigma = 400 \text{ nH}$ , inductive load	$T_{vj} = 25 \text{ °C}$	260		ns
			$T_{vj} = 125 \text{ °C}$	330		ns
			$T_{vj} = 150 \text{ °C}$	360		ns
Turn-on switching energy	$E_{on}$	$V_{CC} = 1800 \text{ V}$ , $I_C = 250 \text{ A}$ , $R_G = 10 \text{ }\Omega$ , $C_{GE} = 0 \text{ nF}$ , $V_{GE} = \pm 15 \text{ V}$ , $L_\sigma = 400 \text{ nH}$ , inductive load	$T_{vj} = 25 \text{ °C}$	360		mJ
			$T_{vj} = 125 \text{ °C}$	460		mJ
			$T_{vj} = 150 \text{ °C}$	515		mJ
Turn-off switching energy	$E_{off}$	$V_{CC} = 1800 \text{ V}$ , $I_C = 250 \text{ A}$ , $R_G = 10 \text{ }\Omega$ , $C_{GE} = 0 \text{ nF}$ , $V_{GE} = \pm 15 \text{ V}$ , $L_\sigma = 400 \text{ nH}$ , inductive load	$T_{vj} = 25 \text{ °C}$	330		mJ
			$T_{vj} = 125 \text{ °C}$	445		mJ
			$T_{vj} = 150 \text{ °C}$	480		mJ
Short circuit current	$I_{SC}$	$t_{psc} \leq 10 \text{ }\mu\text{s}$ , $V_{GE} = 15 \text{ V}$ , $V_{CC} = 2500 \text{ V}$ , $V_{CEM \text{ CHIP}} \leq 3300 \text{ V}$	$T_{vj} = 150 \text{ °C}$	1090		A

<sup>3)</sup> Characteristic values according to IEC 60747 - 9

<sup>4)</sup> Collector-emitter saturation voltage is given at chip level

## Diode characteristic values <sup>5)</sup>

Parameter	Symbol	Conditions	min	typ	max	Unit	
Forward voltage <sup>6)</sup>	$V_F$	$I_F = 250 \text{ A}$	$T_{vj} = 25 \text{ }^\circ\text{C}$	2.05	2.5	V	
			$T_{vj} = 125 \text{ }^\circ\text{C}$		2.25	2.6	V
			$T_{vj} = 150 \text{ }^\circ\text{C}$		2.2		V
Reverse recovery current	$I_{rr}$		$T_{vj} = 25 \text{ }^\circ\text{C}$	280		A	
			$T_{vj} = 125 \text{ }^\circ\text{C}$		320		A
			$T_{vj} = 150 \text{ }^\circ\text{C}$		330		A
Recovered charge	$Q_{rr}$	$V_{CC} = 1800 \text{ V},$ $I_F = 250 \text{ A},$ $V_{GE} = \pm 15 \text{ V},$ $R_G = 10 \text{ }^\Omega, C_{GE} = 0 \text{ nF},$ $di/dt = 1 \text{ kA}/\mu\text{s}$ $L_\sigma = 400 \text{ nH}, \text{ inductive load}$	$T_{vj} = 25 \text{ }^\circ\text{C}$	170		$\mu\text{C}$	
			$T_{vj} = 125 \text{ }^\circ\text{C}$		270		$\mu\text{C}$
			$T_{vj} = 150 \text{ }^\circ\text{C}$		320		$\mu\text{C}$
Reverse recovery time	$t_{rr}$		$T_{vj} = 25 \text{ }^\circ\text{C}$	1160		ns	
			$T_{vj} = 125 \text{ }^\circ\text{C}$		1580		ns
			$T_{vj} = 150 \text{ }^\circ\text{C}$		1830		ns
Reverse recovery energy	$E_{rec}$		$T_{vj} = 25 \text{ }^\circ\text{C}$	180		mJ	
			$T_{vj} = 125 \text{ }^\circ\text{C}$		310		mJ
			$T_{vj} = 150 \text{ }^\circ\text{C}$		370		mJ

<sup>5)</sup> Characteristic values according to IEC 60747 - 2

<sup>6)</sup> Forward voltage is given at chip level

## Package properties <sup>7)</sup>

Parameter	Symbol	Conditions	min	typ	max	Unit
IGBT thermal resistance junction to case	$R_{th(j-c)IGBT}$				0.051	K/W
Diode thermal resistance junction to case	$R_{th(j-c)DIODE}$				0.102	K/W
IGBT thermal resistance <sup>2)</sup> case to heatsink	$R_{th(c-s)IGBT}$	IGBT per switch, $\lambda$ grease = $1\text{W}/\text{m} \times \text{K}$		0.048		K/W
Diode thermal resistance <sup>2)</sup> case to heatsink	$R_{th(c-s)DIODE}$	Diode per switch, $\lambda$ grease = $1\text{W}/\text{m} \times \text{K}$		0.096		K/W
Comparative tracking index	CTI			> 600		
Module stray inductance	$L_{\sigma CE}$			125		nH
Resistance, terminal-chip	$R_{CC'+EE'}$	per switch	$T_C = 25 \text{ }^\circ\text{C}$	0.25		m $\Omega$
			$T_C = 125 \text{ }^\circ\text{C}$	0.33		
			$T_C = 150 \text{ }^\circ\text{C}$	0.35		


<sup>2)</sup> For detailed mounting instructions refer to ABB Document No. 5SYA 2039

## Mechanical properties <sup>7)</sup>


Parameter	Symbol	Conditions	min	typ	max	Unit
Dimensions	L x W x H	Typical		73 x 140 x 48		mm
Clearance distance in air	$d_a$	according to IEC 60664-1 and EN 50124-1	Term. to base:	35		mm
			Term. to term:	19		
Surface creepage distance	$d_s$	according to IEC 60664-1 and EN 50124-1	Term. to base:	64		mm
			C1 to E1:	54		
			C1 to E2:	78		
Mass	m			620		g

<sup>7)</sup> Package and mechanical properties according to IEC 60747 - 15

## Electrical configuration



## Outline drawing <sup>2)</sup>



Note: all dimensions are shown in millimeters

<sup>2)</sup> For detailed mounting instructions refer to ABB Document No. 5SYA 2039

This is an electrostatic sensitive device, please observe the international standard IEC 60747-1, chap. IX.  
This product has been designed and qualified for Industrial Level.




Fig. 1 Typical on-state characteristics, chip level




Fig. 2 Typical transfer characteristics, chip level




Fig. 3 Typical output characteristics, chip level




Fig. 4 Typical output characteristics, chip level




Fig. 5 Typical switching energies per pulse vs. collector current




Fig. 6 Typical switching energies per pulse vs. gate resistor




Fig. 7 Typical switching times vs. collector current




Fig. 8 Typical switching times vs. gate resistor




Fig. 9 Typical capacitances vs. collector-emitter voltage




Fig. 10 Typical gate charge characteristics




Fig. 11 Turn-off safe operating area (RBSOA)




Fig. 12 Typical reverse recovery characteristics vs. forward current




Fig. 13 Typical reverse recovery characteristics vs. di/dt




Fig. 14 Typical diode forward characteristics chip level




Fig. 15 Safe operating area diode (SOA)






Fig. 16 Thermal impedance vs. time

Analytical function for transient thermal impedance:

$$Z_{th(j-c)}(t) = \sum_{i=1}^n R_i (1 - e^{-t/\tau_i})$$

	i	1	2	3	4	5
IGBT	Ri(K/kW)	35.1	8.25	3.84	3.79	
	$\tau_i$ (ms)	207.4	30.1	7.6	1.6	
DIODE	Ri(K/kW)	69.2	17.3	7.37	7.77	
	$\tau_i$ (ms)	203.6	30.1	7.5	1.6	

**Related documents:**

- 5SYA 2042 Failure rates of HiPak modules due to cosmic rays
- 5SYA 2043 Load - cycle capability of HiPaks
- 5SYA 2045 Thermal runaway during blocking
- 5SYA 2053 Applying IGBT
- 5SYA 2058 Surge currents for IGBT diodes
- 5SYA 2093 Thermal design of IGBT modules
- 5SYA 2098 Paralleling of IGBT modules
- 5SZK 9111 Specification of environmental class for HiPak Storage
- 5SZK 9112 Specification of environmental class for HiPak Transportation
- 5SZK 9113 Specification of environmental class for HiPak Operation (Industry)
- 5SZK 9120 Specification of environmental class for HiPak

ABB Switzerland Ltd.  
Semiconductors  
Fabrikstrasse 3  
CH-5600 Lenzburg  
Switzerland

Phone: +41 58 586 1419  
Fax: +41 58 586 1306  
E-Mail: [abbsem@ch.abb.com](mailto:abbsem@ch.abb.com)  
Internet: [www.abb.com/semiconductors](http://www.abb.com/semiconductors)

We reserve the right to make technical changes or to modify the contents of this document without prior notice.

We reserve all rights in this document and the information contained therein. Any reproduction or utilization of this document or parts thereof for commercial purposes without our prior written consent is forbidden.

Any liability for use of our products contrary to the instructions in this document is excluded.