

IEC**IECEE**

Ref. Certif. No.

CN58854

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME**CB TEST CERTIFICATE**

Product

Contactors for capacitor switching

Name and address of the applicant

ABB France
11 Rue d'Arsonval 69680, Chassieu, FRANCE

Name and address of the manufacturer

ABB France
11 Rue d'Arsonval 69680, Chassieu, FRANCE

Name and address of the factory

Note: When more than one factory, please report on page 2

ABB Bulgaria EOOD – Rakovski branch
14-18 Industrial Road 1, Industrial Zone Rakovski, Region
Plodiv, 4142 Stryama, Bulgaria

Ratings and principal characteristics

See appendix for the specification

Trademark / Brand (if any)

ABB

Customer's Testing Facility (CTF) Stage used

N/A

Model / Type Ref.

UA50,UA63,UA75

Additional information (if necessary may also be reported on page 2)

A sample of the product was tested and found to be in conformity with

IEC 60947-4-1:2018

As shown in the Test Report Ref. No. which forms part of this Certificate

00901-CB2022CQC-104364

This CB Test Certificate is issued by the National Certification Body

CHINA QUALITY CERTIFICATION CENTRESection 9, No. 188 Nansihuan Xilu, Beijing 100070 P. R. China
Tel: +86-10-83886666 Fax: +86-10-83886282
website: <http://www.cqc.com.cn>

Date: Feb.14,2023

Signature:

Xie ZhaoXu

CB 0070822

UA50,UA63,UA75

U_{imp}:8kV;

U_i: 1000V;

UA50:

I_{th}:100A;

AC-6b: U_e/Q_e:220-230-240V/20kvar,400-415V/33kvar,440V/36kvar,
500-550V/40kvar,660-690V/55kvar;

I_e:51A;

UA63:

I_{th}:125A;

AC-6b: U_e/Q_e:220-230-240V/25kvar,400-415V/45kvar,440V/50kvar,
500-550V/50kvar,660-690V/70kvar;

I_e:66A;

UA75:

I_{th}:125A;

AC-6b: U_e/Q_e:220-230-240V/30kvar,400-415V/50kvar,440V/55kvar,
500-550V/62kvar,660-690V/75kvar;

I_e:76A;

U_s: 24V 50/60Hz,42V 50/60Hz, 48V 50/60Hz,110V 50Hz/110-120V 60Hz,
220-230V 50Hz/230-240V 60Hz,380-400V 50Hz/400-415V 60Hz,
400-415V 50Hz/415-440V 60Hz;

IP10;

3P;

Auxiliary contacts:(CAL5-11)(CQC2013010304604041)

I_{th}:16A;

AC-15:U_e/I_e: 24~127V/6A, 220~240V/4A, 380~440V/3A, 500~690V/2A;

DC-13:U_e/I_e: 24V/6A, 48V/2.8A, 72V/1A, 110~125V/0.55A, 220~250V/0.3A;

1NO1NC

Page 1 of 1

Additional information (if necessary)

Date: Feb.14,2023

Signature:

谢肇煦

Xie ZhaoXu