



Test Report				Date of issue: 25.5.2015							
Customer:				Serial No.:							
Customer ref.:				Order No.:							
				Type: M3GP 160MLC 2							
				Product Code: 3GGP161430-ADK							
				Protection type: Ex tb IIIB/C T125C Db							
				Cert. No.: LCIE 13 ATEX 3067 X / IECEx LCIE 13.0047 X							
Rating:											
		V	Hz	kW	r/min	A	cos φ	Duty			
3-Motor		690	Y 50	18,5	2942	17,9	0,93	S1			
Insul.cl.F		400	D 50	18,5	2942	30,8	0,93	S1			
IP65		660	Y 50	18,5	2935	18,9	0,93	S1			
		380	D 50	18,5	2935	32,6	0,93	S1			
		415	D 50	18,5	2948	30,0	0,92	S1			
		460	D 60	18,5	3551	26,8	0,93	S1			
Eff class IE3		50Hz : IE3-93,1(100%)-93,9(75%)-93,9(50%) 60Hz : IE3-92,9(100%)									
Resistance Line				Ambient: 20,6 °C			Insulation resistance at 22,1 °C		Overload		
U ₁ - V ₁				0,2242 Ω			R > 2000 Mohm 1000 V		Current 150 % 120s		
U ₁ - W ₁				0,2234 Ω					Torque 160 % 15s		
V ₁ - W ₁				0,2238 Ω					Speed 120 % 120s		
				High-voltage test winding			2400 V		60 s		
Test	Torque [Nm]	Line U[V]	f[Hz]	Input I[A]	P1 [kW]	Output P2 [kW]	n[r/min]	cos φ	η [%]		
No load test		399 D	50	8,1	0,41		3000	0,07			
Locked rotor test		60 D	50	32,9	1,34		0	0,39			
Thermal test (100% load)	60,0	400 D	50	31,6	19,91	18,50	2947	0,91	92,90		
Partial load points:											
~75% load	44,3	400 D	50	23,9	14,70	13,75	2962	0,89	93,50		
~50% load	28,2	400 D	50	16,7	9,44	8,80	2976	0,81	93,27		
~25% load	13,9	400 D	50	11,1	4,81	4,34	2989	0,62	90,22		
Temperature rise at rated load.				°C	[K]	Method		Measurement method			
Stator winding :				49,5	1			1 Resistance			
Frame :				27,8	2			2 Thermometer			
Bearing D-end :				31,4	2			3 Thermocouples			
Ambient Temperature :				22	2						
<p>These tests have been carried out on motor no. 3GV12108464070004, on date 2012-01-18 which is identical in electrical design with the above.</p> <p>Manufactured and tested in accordance with rules of IEC 60034-1 and IEC 60034-2-1. PLL determined from residual loss.</p>											
On behalf of customer											
On behalf of manufacturer				Date of test							
Tested by ABB AB, LV Motors, 721 70 Västerås, Sweden						Telephone +46 (0)21 32 90 00		Telefax +46 (0)21 32 90 22			

Computer print-out valid without signature.