


On-load tap-changer type UCGL./III, VUCGL./III, UCLL./III, UC DL./III, 8 tap positions, linear switching.
 Max. effective No. of turns in pos. 1.
 The tap-changer is delivered set in pos. 5, the preceding pos. was 4.

Lindningskopplare typ UCGL./III, VUCGL./III, UCLL./III, UC DL./III, 8 lägen, linjär koppling.
 Max. antal effektiva varv i läge 1.
 Lindningskopplaren levereras inställd i läge 5, föregående läge var 4.

Pos. Läge	Tap selector and diverter switch connect	30
1	1-V-x	
2	2-H-v	
3	3-V-x	
4	4-H-v	
5	5-V-x	
6	6-H-v	
7	7-V-x	
8	8-H-v	



The tap-changer is shown in pos. 5, the preceding pos. was 4.
 The tap selector is seen from above.
 Contact arm V is located above contact arm H.

Lindningskopplaren visad i läge 5, föregående läge var 4.
 Väljaren sedd uppifrån.
 Kontaktarm V ligger över kontaktarm H.

Continuous lines show leads included in the tap-changer. Dashed lines show leads belonging to the cleats and leads.

Heldragna linjer visar ledare som ingår i lindningskopplaren. Streckade linjer visar ledare som tillhör anslutningsdonet.

Drawn by Form No.	Sheet	Year	Week	Cont
	Dept	Rev Ind	Revision	Appd
	Year	Year	Week	
	Accepted by qual control	Accepted for prod by	Description (English) CONNECTION DIAGRAM	
Design checked by	G.Andersson SA	Drawn by	T.Larsen	Description (own language) KOPPLINGSSCHEMA
	Drawing checked by	A.Hultberg	Issued by Dept	Year
	Week	COM/FOK	07	49
ABB		Asea Brown Boveri		5492 0367-14
Lang	Sheef	Revind	Cont	
	1	-	-	
DATAORIGINAL		File name		
		0367-14		

We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden. © ABB '19