



Type Test Report				Date of issue: 4.6.2014						
Customer: ABB OY				Serial No.: 3GF12103384						
Order No.: 627894-1 Type: M3JP 225SMC 4 IMB3/IM1001 Product Code: 3GJP222230-ADG Protection type: Ex d IIB T4 Gb Cert. No.: LCIE 10 ATEX 3057X / IECEx LCI 04.0005X										
Rating:										
				V	Hz	kW	r/min	A	cos φ	Duty
3-Motor				690	Y 50	45	1477	45,4	0,88	S1
Insul.cl.F				400	D 50	45	1477	78,4	0,88	S1
IP55				415	D 50	45	1479	77,3	0,86	S1
Eff class IE2				50Hz : IE2-94.1%(100%)-94.6%(75%)-94.4%(50%)						
Resistance Line				Ambient: 22,0 °C		Insulation resistance at 42,5 °C			Overload	
U ₁ - V ₁				0,08011 Ω		4900 MΩ			1000 V	
U ₁ - W ₁				0,08011 Ω					Torque 160 % 15s	
V ₁ - W ₁				0,08028 Ω						
				High-voltage test winding			2900 V		1 s	
Test	Torque [Nm]	Line U[V]	f[Hz]	Input I[A]	P1 [kW]	Output P2 [kW]	n[r/min]	cos φ	η [%]	
No load test		400,1 D	50	25,4	1,00		1500	0,06		
Locked rotor test		79,8 D	50	78,4	3,91		0	0,36		
Thermal test (100% load)	291,0	400,1 D	50	81,5	48,1	45,0	1480	0,85	93,5	
Partial load points:										
~75% load	217,8	400,0 D	50	62,5	35,9	33,8	1486	0,83	93,9	
~50% load	145,0	400,1 D	50	45,6	24,0	22,5	1491	0,76	93,7	
~25% load	72,6	400,1 D	50	31,8	12,4	11,3	1495	0,56	90,8	
Temperature rise at rated load.				[°C]	[K]	Method		Measurement method		
Stator winding :					62,8	1		1 Resistance		
Frame :					26,6	2		2 Thermometer		
Bearing D-end :					45,4	2		3 Thermocouples		
Rotor :						3				
Ambient Temperature :				25,0		2				
Manufactured and tested in accordance with rules of IEC 60034-1 and IEC 60034-2-1. PLL determined from residual loss.										
On behalf of customer										
On behalf of manufacturer				Date of test		18.3.2012				
Tested by ABB Oy, Motors and Generators, Vaasa, Finland						Telephone +358 10 2211 Telefax +358 10 22 47372				

Computer print-out valid without signature.

ABB, Motors and Generators
www.abb.com/motors&generators