

DATA SHEET

# ABB Ability™ Smart Sensor

## Condition monitoring for pumps



The ABB Ability™ Smart Sensor converts traditional pumps into smart, wirelessly connected devices. It enables you to monitor the health of your pumps, identify inefficiencies and improve reliability and safety.

### Intended use

- Single-stage, overhung/vertical, suction-end centrifugal pumps
- Channel or vortex impellers
- Fluid type: water, wastewater or similar
- Pump shaft height: 150 mm to 450 mm
- Fixed or variable-speed driven

### ABB Ability™ Smart Sensor gateway

Automatically collects data from a high number of Smart Sensors and transmits the data to the cloud for processing.

### Gateway specifications

Range	Approx. 50 m (can vary in an industrial environment depending on facility layout)
Power supply	Power supply over ethernet port
Certifications	1879 FCC, CSA, CE
Radio frequency	ISM band, 2.402-2.480 GHz
Data transfer	WiFi, LAN 4G/LTE USB dongle
Environment	Operating temperature: -40 °C to +65 °C


### Health parameters

- Overall condition
- Overall vibration (velocity rms)
- Bearing condition
- Misalignment
- Unbalance
- Looseness
- Blade problems
- Skin temperature (degrees)

### Operating parameters

- Radial vibration (velocity rms)
- Tangential vibration (velocity rms)
- Axial vibration (velocity rms)
- Speed (rpm)
- Operating hours
- Number of starts

<b>SPECIFICATIONS</b>	
<b>Temperature measurement</b>	
Measurement range	-40 °C to +80 °C
Resolution	0.05 °C
Accuracy (baseplate temperature)	+/-0.5 °C
<b>Vibration measurement (overall velocity values)</b>	
Amplitude range	0.04 - 700 mm/s (25 Hz)
Frequency range	10 Hz - 1 kHz
<b>Wireless communication</b>	
Network / radio standard	Bluetooth® 4.0 / IEEE 802.15.1
Frequency	2.4 GHz, license free ISM band
Range	With mobile phone: 1 - 10 m With gateway: approx. 50 m (can vary in an industrial environment depending on the facility layout)
<b>Power</b>	
Battery type (not replaceable)	3.0 V Lithium Permanganate (LI-MnO4) button cell CR2477N
Estimated battery lifetime	Batteries have a design life of 5 years. Expect 3 - 6 years depending on usage, settings and temperatures
Measured skin temperature (°C)	+40 °C      +70 °C
Battery life in years, sensor in default configuration	approx. 5      approx. 3
Default configuration: Sensor measures once per hour and stores data to memory. Stored data must be collected at least monthly with a Bluetooth® mobile device or gateway.	
<b>Environmental</b>	
Temperature	Operation: -40 °C to +80 °C Storage: +10 °C to +25 °C (due to battery life)
IP class	IP66 (dust-tight and resistant to powerful water jetting)
Vibration (of mounted surface)	<15 g at 100 Hz
<b>Certifications</b>	
CE, FCC, IC, RCM, EAC, UL, C-UL, SRE, SUBTEL	
Safe areas only; no hazardous area certification	
<b>Physical</b>	
Weight	0.26 kg
Case material	Stainless steel (316)/Thermoplastic (PA6-GF30 (Akulon® Ultraflow K-FKGS6 /B))
Mounting	On housing above drive-end bearing of the pump (the bearing closest to the motor when seen from the pump), parallel to pump shaft; ensure good contact Ensure that correct mounting kit is used; ready-made mounting kits might not be available for all kinds of pumps



For more information please visit:  
[www.abb.com/smartsensor](http://www.abb.com/smartsensor)

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB Ltd does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB Ltd. Copyright© 2019 ABB  
All rights reserved