



Ref. Certif. No.

CN53290

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Contactor

Name and address of the applicant

ABB France
2 rue d'Arsonval 69680 Chassieu France

Name and address of the manufacturer

ABB France
2 rue d'Arsonval 69680 Chassieu France

Name and address of the factory

ABB Xinhui Low Voltage Switchgear Co.,Ltd.
Jinguzhou Industrial Development Zone, Xinhui Region,
Jiangmen City, Guangdong Province, P.R.China

Note: When more than one factory, please report on page 2

Additional information on page 2

Ratings and principal characteristics

See the Appendix

Trademark / Brand (if any)

ABB

Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

AX06-30, AX09-30, AX12-30, AX18-30, AX25-30

Additional information (if necessary may also be reported on page 2)

IEC 60947-4-1:2018

A sample of the product was tested and found to be in conformity with

As shown in the Test Report Ref. No. which forms part of this Certificate

00901-CB2020CQC-095677

This CB Test Certificate is issued by the National Certification Body

CHINA QUALITY CERTIFICATION CENTRE

Section 9, No. 188 Nansihuan Xilu, Beijing 100070 P. R. China
Tel: +86-10-83886666 Fax: +86-10-83886282
website: <http://www.cqc.com.cn>



Date: Apr.12,2021

Signature:

Lu Mei

CB 0062641

Name of the factory	Address of the factory
1.ABB SA	RUTA NACIONAL 157 KM 1233 5 BELLA VISTA POST 4168 TUCUMAN ARGENTINA
2.ABB Bulgaria EOOD - Rakovski branch	BULGARIA, 4142 Village of Stryama, Region of Plovdiv, Municipality of Rakovski, Rakovski Industrial Zone, 14 Industrial Road 1, nr,14-18

Additional information (if necessary)

Date: Apr.12,2021

Signature: 


Lu Mei

AX06-30,AX09-30,AX12-30,AX18-30,AX25-30;
Uimp: 6kV;
Ui:690V;
AX06-30:
Ith: 22A;
AC-1:Ue/Ie:690V/20A;
AC-3:Ue/Ie:220-230-240V/7A,380-400V/7A,415V/7A,440V/7A,500V/6A,690V/5A;
AC-8a:Ue/Ie:400V/9A;
AX09-30:
Ith: 24A;
AC-1:Ue/Ie:690V/22A;
AC-3:Ue/Ie:220-230-240V/9A,380-400V/9A,415V/9A,440V/9A,500V/9A,690V/7A;
AC-8a:Ue/Ie:400V/12A;
AX12-30:
Ith: 26A;
AC-1:Ue/Ie:690V/25A;
AC-3:Ue/Ie:220-230-240V/12A,380-400V/12A,415V/12A,440V/9A,500V/9A,690V/7A;
AC-8a:Ue/Ie:400V/16A;
AX18-30:
Ith: 28A;
AC-1:Ue/Ie:690V/27A;
AC-3:Ue/Ie:220-230-240V/18A,380-400V/18A,415V/18A,440V/12A,500V/12A,690V/9A;
AC-8a:Ue/Ie:400V/22A;
AX25-30:
Ith: 32A;
AC-1:Ue/Ie:690V/32A;
AC-3:Ue/Ie:220-230-240V/25A,380-400V/25A,415V/25A,440V/16A,500V/14A,690V/10A;
AC-8a:Ue/Ie:400V/30A;
Us: 24V 50/60Hz,48V 50/60Hz,105V 50Hz/110-127V 60Hz, 110V 50Hz/110-120V 60Hz,
190V 50Hz/220V 60Hz, 200V 50Hz/200-220V 60Hz, 220-230V 50Hz/230-240V 60Hz,
230-240V 50Hz/240-260V 60Hz, 380-400V 50Hz/400-415V 60Hz, 400-415V 50Hz/415-440V

Page 1 of 2

Additional information (if necessary)

Date: Apr.12,2021

Signature: 
Lu Mei

60Hz;

3P;

IP20;

Auxiliary contact:(body contact)

1NO,1NC;

Ith:16A;

AC-15:Ue/Ie: 24-127V/6A,220-240V/4A,380-440V/3A, 500V/2A, 690V/2A;

DC-13:Ue/Ie: 24V/6A, 48V/2.8A, 72V/2A, 125V/1.1A, 250V/0.55A

Page 2 of 2

Additional information (if necessary)

Date: Apr.12,2021

Signature:



Lu Mei