

PANEL MARKS: RNSB12G9645R

TECHNICAL SPECIFICATIONS

PANEL TYPE: ReliaGear neXT SuperBox
 QUANTITY: 1
 AMPS: 1200A
 VOLTAGE: Up to 600V
 SYSTEM: 3P3W or 3P4W
 KAIC: Up to 200 KAIC SC FULLY RATED
 MATERIAL: COPPER BUS
 PLATE: SILVER PLATE
 ENCLOSURE: NEMA 3R
 MOUNTING: SURFACE

MAIN DISCONNECT DEVICE

FEED DIR. Bottom
 TYPE: Breaker
 AMPS: 1200A
 POLES: 3

INTERIOR X-VALUES



TOTAL X BUS AVAILABLE X BUS
 32 32

OPTIONS INCLUDED

QTY	DESCRIPTION
1	Copper Bus Heat Rated
1	47 Ckt bonded grd

BOM

QTY	CAT #	DESCRIPTION
1	GDBG47AL	Ground
1	IN3212NN3H2	Bus
1	NL1210G7X7BAL	Neutral
1	ER9645R	Enclosure
1	IF3245F	Frame
1	FT45S00155	Front 1 of 2
1	FT45S00325	Front 2 of 2
1	GC45F32NNA	Gutter
1	300127626P445	GF Mounting Rail
9	SR03BF	Spacer
9	SR03BB	Spacer
2	SR02BF	Spacer
2	SR02BB	Spacer
1	SR01BF	Spacer
1	SR01BB	Spacer



PANEL INFORMATION	
INTERNAL DIMENSIONS	96"X47"X11"
NOTES	
EXTERNAL DIMENSIONS	97"X48.5"X16.7"

1. FML - FRAME MOUNTING LOCATION.
2. DRAWING NOT TO SCALE.
3. DIMENSIONS ARE IN INCHES[mm].

NEUTRAL ARE PRESSURE LUGS.

PROJECT NAME :	ABB	PANEL ID:	PRODUCT NAME:	DRAWING NO:
CUSTOMER:		CREATED BY:	ReliaGear neXT	ITEM NO:
		DATE:	PANELBOARD	MARKS:
		REVISION NO.		QUOTE NO:
				SHEET: