

S = { Ø11 – Special IM 2001/\*11  
M8 – Special IM 2101/\*11

**M2AA 112**  
(\* Except 112 MC

Additional information:

VC005: Metal protective roof, vertical motor, shaft down / Doble protector de ventilador


VC226: Flange ring FF 130 / Aro brida FF 130 // VC227: Flange ring FT 130 / Aro brida FT 130

## Motor Dimension Print

Motor Type :  
M2AA 112 (\*)

Document Nº :  
3GZE 500 110-941.005

Description : Motor foot and flange mounted special (2-pieces) IM2001/\*11 or IM2101/\*11  
Motor con patas y brida (2 piezas) IM2001/\*11 o IM2101/\*11



Unit : Discret Automation & Motion - Fábrica Motores  
Date : 2012-12-12

Issued by : ERM/ A. Caubera  
Approved by : ERM/ G. Blanes

Replaces :  
Replaced by :

**Asea Brown Boveri, S.A.**

Customer Reference :

**ABB**