

Certificate of Conformity

LOVAG-Certificate No. FR 01-006a

Cancel and supersede the lovag certificate n° FR 01-006

Apparatus : Enclosed contactor

Designation : A75-30-11

Manufacturer or responsible vendor

ABB CONTROL
10, rue Ampère - ZI - BP 114
69685 CHASSIEU - FRANCE

Tested for: ABB CONTROL

Tested by: ASEFA platform G03

This Certificate applies only to the apparatus tested. The responsibility for conformity of any apparatus having the same designation with that tested rests with the manufacturer or responsible vendor.

This certificate has been prepared according to LOVAG (Low Voltage Agreement Group) Objectives and Operating Principles of mutual recognition. The responsible certification body as member of LOVAG issues a Certificate of Conformity with the above mentioned Standard(s) following the exclusive use of LOVAG Test Instructions wherever applicable.

Only integral reproduction of this Certificate or reproductions of this page accompanied by any page(s) on which are stated the tests performed and the assigned rated characteristics of the apparatus tested, are permitted without written permission from the LOVAG Signatory responsible for this Certificate.

The apparatus, constructed in accordance with the description mentioned in the Test Report, listed on this Certificate has been subjected to the series of proving tests in accordance with IEC 60947-4-1(1990-05) corrigendum (1991-12) amendment 1 (1994-11) and amendment 2 (1996-08) - EN 60947-4-1 (1992-01) amendment 1 (1995-01) and amendment 2 (1997-06) - NFEN 60947-4-1(1993-02) amendment 1 (1995-04) and amendment 2 (1997-12) test sequences II and III. The results are shown in the Test Report in accordance to LOVAG. The values obtained and the general performance are considered to comply with the above Standard(s) and to justify the characteristic assigned by the manufacturer as stated below.


Main circuit 3-pole $U_i = 1000 \text{ V}$ $I_{th} = 125 \text{ A}$
Sequence II (AC4)

$U_e \text{ (V)}$	$\leq 440 \text{ V}$	$>440 \text{ V and } \leq 500 \text{ V}$	$>500 \text{ V and } \leq 690 \text{ V}$
$I_e \text{ (A)}$	75 A	65 A	48 A

Sequence III (AC1) SCPD : fuses 160 AgG
 $U_e = 500 \text{ V}$ $I_e = 125 \text{ A}$ $I'' = 5 \text{ kA}$ $I_q = 25 \text{ kA}$


This document includes Report No.: G03 - 00499
Issue Date: 2000.12.14

Responsible Certification Body



I. HELLER
Authorized Signature

Date: 22 MAI 2001



Certificate of Conformity

LOVAG-Certificate No FR 01-030

Apparatus : contactor

Designation : A 75-30-11

Manufacturer or responsible vendor

ABB CONTROL
 10, rue Ampère - ZI - BP 114
 69685 CHASSIEU - FRANCE

Tested for: ABB CONTROL

Tested by: ASEFA platform G11

This Certificate applies only to the apparatus tested. The responsibility for conformity of any apparatus having the same designation with that tested rests with the manufacturer or responsible vendor.

This certificate has been prepared according to LOVAG (Low Voltage Agreement Group) Objectives and Operating Principles of mutual recognition. The responsible certification body as member of LOVAG issues a Certificate of Conformity with the above mentioned Standard(s) following the exclusive use of LOVAG Test Instructions wherever applicable.

Only integral reproduction of this Certificate or reproductions of this page accompanied by any page(s) on which are stated the tests performed and the assigned rated characteristics of the apparatus tested, are permitted without written permission from the LOVAG Signatory responsible for this Certificate.

The apparatus, constructed in accordance with the description mentioned in the Test Report listed on this Certificate has been subjected to the series of proving tests in accordance with IEC 60947-4-1(1990-05) corrigendum (1991-12) amendment 1 (1994-11) and amendment 2 (1995-08) - EN 60947-4-1 (1992-01) amendment 1 (1995-01) and amendment 2 (1997-06) - NFEN 60947-4-1 (1993-02) amendment 1 (1995-04) and amendment 2 (1997-12), tests sequences I and IV. The results are shown in the Test Report in accordance to LOVAG. The values obtained and the general performance are considered to comply with the above Standard(s) and to justify the characteristic assigned by the manufacturer as stated below.

Main circuit: 3-pole $U_i = 1000 \text{ V}$ $U_{imp} = 8 \text{ kV}$ $I_{th}/I_{the} = 125 \text{ A} / 105 \text{ A}$

Rated operational voltage: $U_e(\text{V})$		≤ 240	$> 240 \& \leq 400$	$> 400 \& \leq 415$	$> 415 \& \leq 440$	$> 440 \& \leq 530$	$> 530 \& \leq 690$	$> 690 \& \leq 1000$
Rated operational Current:	$I_e(\text{A}) \text{ AC-1}$	125	125	125	125	125	125	-
	$I_e(\text{A}) \text{ AC-3}$	75	75	72	70	65	48	28
	$I_e(\text{A}) \text{ AC-4}$	75	75	72	70	65	48	28

This document includes Report No.: G11 20011311
 Issue Date: 2001.10.01

Responsible Certification Body


 I. HELLER
 Authorized Signature

Date: 25 OCT. 2001