


On-load tap-changer type VUBBL, UBBL, 10 tap positions, linear switching.
 Min effective No. of turns in pos 1.
 The tap-changer is delivered set in pos 5.


Lindningskopplare typ VUBBL, UBBL, 10 lägen, linjär-koppling.
 Min antal effektiva varv i läge 1.
 Lindningskopplaren levereras inställd i läge 5.

Pos Läge	H connects förbinder
1	10 - 15
2	9 - 15
3	8 - 15
4	7 - 15
5	6 - 15
6	5 - 15
7	4 - 15
8	3 - 15
9	2 - 15
10	1 - 15

We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden.
 © ABB '19



1) OUTPUT TERMINAL
STRÖMAVTAGNING
 *) FOR VUBB TYPE OF OLTC
I VUBB UTFÖRANDE



1) Internal connections between the terminals 15 of the three phases are included in the star-point type. Dashed lines show in delivery not included leads belonging to cleats and leads.

H Main contact
Huvudkontakt

Inre förbindningar mellan uttag 15 i de tre faserna ingår i nollpunktsutförande. Streckade linjer visar i leveransen ej ingående ledare tillhörande anslutningsdonet.

Sheet	Cont
	Year Week
Form No.	Dept
	Year Week
Design checked by	Rev Ind
	Revision
Design checked by	Appd
	Year Week

3	Output for VUBB type added.	DAAN	20	14
2	VUBBL added.	TL	10	27
1	Selector switch changed position.	SK	08	36

Accepted by qual control R.Yngvesson	Accepted for prod by	Description (English) CONNECTION DIAGRAM	DATAORIGINAL
Design checked by B-O.Stenestam	Drawn by L.Bergman	Description (own language) KOPPLINGSSCHEMA	File name 0390-6
Drawing checked by M.Hedlund	Issued by Dept Year Week COM/TKO 97 32	5492 0390-6	Lang 1
ABB	Asea Brown Boveri		Rev Ind 3