

S = { Ø13 – Special IM 3001/\*11  
 M10 – Special IM 3601/\*11

**M2AA 112**  
 (\*) Except 112 MC

**Additional information:**

VC005: Metal protective roof, vertical motor, shaft down / Doble protector de ventilador


VC233: Flange ring FF 165 / Aro brida FF 165 // VC234: Flange ring FT 165 / Aro brida FT 165

**Motor Dimension Print**

Motor Type :  
 M2AA 112 (\*)

Document Nº :  
 3GZE 500 112-951.005

Description : **Motor foot and flange mounted special (2-pieces) IM3001/\*11 or IM3601/\*11**  
**Motor con patas y brida (2 piezas) IM3001/\*11 o IM3601/\*11**



Unit : **Discret Automation & Motion - Fábrica Motores**  
 Date : **2012-12-12**

Issued by : **ERM/ A. Caubera**  
 Approved by : **ERM/ G. Blanes**

Replaces :  
 Replaced by :

**Asea Brown Boveri, S.A.**

Customer Reference :

**ABB**