


We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden.
© ABB '19

On-load tap-changer type (V)UCGL./F, (V)UCLL./F, UCCL./F,
7 positions, linear switching.
Min. effective No. of turns in pos. 1.
The tap-changer is delivered set in pos. 4,
the preceding pos. was 3.

Lindningskopplare typ (V)UCGL./F, (V)UCLL./F, UCCL./F,
7 lägen, linjär koppling.
Min antal effektiva varv i läge 1.
Lindningskopplaren levereras inställd i läge 4,
föregående läge var 3.

Pos. Läge	Tap selector and diverter switch connect	
1	1-V-x	30
2	2-H-v	
3	3-V-x	
4	4-H-v	
5	5-V-x	
6	6-H-v	
7	7-V-x	



The tap-changer is shown in pos. 4,
the preceding pos. was 3.
The tap selector is seen from above.
Contact arm V is located above contact arm H.

Lindningskopplaren visad i läge 4,
föregående läge var 3.
Väljaren sedd uppifrån.
Kontaktarm V ligger över kontaktarm H.

Continuous lines show leads included in the
tap-changer. Dashed lines show leads belonging
to the cleats and leads.

Heldragna linjer visar ledare som ingår i
lindningskopplaren. Streckade linjer visar
ledare som tillhör anslutningsdonet.

Sheet	Cont	Year	Week	Rev Ind			Appd			Year			Week	
				Rev Ind	Revision	Accepted by qual control	Accepted for prod by	Appd	Year	Week	Year	Week	Lang	Sheet
Rev Ind	L.Oberg	Accepted by qual control	Accepted for prod by	M.Haggmar	Description (English)			CONNECTION DIAGRAM			DATA ORIGINAL			
Design checked by	H.Sundberg	Design checked by	Drawn by	A.Wang	Description (own language)			KOPPLINGSSHEMA			File name			
Drawing checked by	N.Gustavsson	Drawing checked by	Issued by Dept	CO/TK	Year	14	Week	02	1ZSC004308-AAC			Lang	Sheet	
				Rev Ind		Cont	-							