


MULTIPLES OF CURRENT RATING (In)



**Time Current Curve**

Available Ratings (Amperes)

Type	Model	Trip Unit	Frame Amps	Current Rating (In)
MCCB	XT4	Ekip Touch/Hi-Touch	250	100 225 150 250

Voltage Rating: 600Vac, 50 to 60 hz systems

electrification.us.abb.com

**Molded Case Circuit Breaker**

**Type Tmax XT4 with Ekip Touch/Hi-Touch LSIG**  
Long Time Curve: IEC-SI

**Operating Conditions:** Curves apply at 50 to 60 Hertz and ambient temperature from -25°C to +70°C up to an altitude of 2000 meters. Electronic trip units do not undergo any variations in performance as the temperature varies, but, in the case of temperatures exceeding +40°C, the maximum setting for protection L (protection against overloads) must be reduced, as indicated in the UL Catalog.

**ABB**

**Reduced Energy Let Through (RELT):** is adjusted by engaging and setting the second instantaneous function (2I-50). The setting range and increments are identical to the primary instantaneous (I-50).

**Instantaneous Override:** When instantaneous protection is turned off, the breaker will immediately trip for any current that is equal to or greater than 3,300A minus 10% or plus 6.06%.

**Additional Long Time Curve Options:** Refer to the following TCCs for other long time delay curve types.  
**I2T** (Standard Inverse Time): 9AKK108468A0722  
**VI** (Very Inverse): 9AKK108468A0720  
**EI** (Extremely Inverse): 9AKK108468A0719  
**I4T** (Fuse Response): 9AKK108468A0718  
**Ground Fault:** 9AKK108468A0717