



## NLRV.E137861 Motor Controllers, Manual

[Page Bottom](#)

### Motor Controllers, Manual

[See General Information for Motor Controllers, Manual](#)

ABB STOTZ-KONTAKT GMBH  
EPPELHEIMER STR 82  
69123 HEIDELBERG, GERMANY

E137861

Investigated to ANSI /UL 508

Accessory AUXILIARY CONTACTS Model(s) HK-01#, HK-10#, HKF1-01#, HKF1-10#, SK1-01#, SK1-10#

UA1-20

Accessory, Enclosures Model(s) IB132 followed by - Y or -G.

Accessory, Panel Mounted Enclosures Model(s) DMS132 followed by - Y or -G.

Investigated to ANSI/UL 60947-1 and ANSI/UL 60947-4-1A

Accessory, current limiters Model(s) S803W-SCL100-SR, S803W-SCL32-SR, S803W-SCL63-SR

Accessory, mounting plates Model(s) PM26-13, PM26-23

Accessory: auxiliary contacts Model(s) AA1-110, AA1-208, AA1-24, AA1-400, AA1-415, AA1-48, AA1-60, CK1-02#, CK1-11#, CK1-20#, HK-02#, HK-11#, HK-20#, HKF1-02#, HKF1-11#, HKF1-20#, SK-02#, SK-11#, SK-20#, UA1-110, UA1-208, UA1-24, UA1-400, UA1-415, UA1-48, UA1-60, UA1-HK-110, UA1-HK-208, UA1-HK-230, UA1-HK-24, UA1-HK-400, UA1-HK-415, UA1-HK-48, UA1-HK-575, UA1-HK-60

Manual motor controllers Model(s) MO132-0.16, MO132-0.25, MO132-0.40, MO132-0.63, MO132-1, MO132-1.60, MO132-10, MO132-12, MO132-16, MO132-2.5, MO132-20, MO132-25, MO132-32, MO132-4, MO132-6.3, MS132-0.16, MS132-0.25, MS132-0.40, MS132-0.63, MS132-1, MS132-1.60, MS132-10, MS132-12, MS132-16, MS132-2.5, MS132-20, MS132-25, MS132-32, MS132-4, MS132-6.3

Manual motor controllers, open type Model(s) M0325-0.16, M0325-0.25, M0325-0.40, M0325-0.63, M0325-1.00, M0325-1.60, M0325-12.5, M0325-16.00, M0325-2.5, M0325-20, M0325-25, M0325-4.00, M0325-6.3, M0325-9.00, MS225-0.16, MS225-0.25, MS225-0.40, MS225-0.63, MS225-1.00, MS225-1.60, MS225-12.5, MS225-16.00, MS225-2.5, MS225-20, MS225-25, MS225-4.00, MS225-6.3, MS225-9.00, MS325-0.16, MS325-0.25, MS325-0.40, MS325-0.63, MS325-1.00, MS325-1.60, MS325-12.5, MS325-16.00, MS325-2.5, MS325-20, MS325-25, MS325-4.00, MS325-6.3, MS325-9.00, MS326-0.16, MS326-0.25, MS326-0.40, MS326-0.63, MS326-1.00, MS326-1.60, MS326-12.5, MS326-16.00, MS326-2.5, MS326-20, MS326-25, MS326-4.00, MS326-6.3, MS326-9.00

Motor disconnects with locking kit SA1, open type Model(s) MS116-0.16, MS116-0.25, MS116-0.40, MS116-0.63, MS116-1.00, MS116-1.60, MS116-10.0, MS116-12.0, MS116-16.0, MS116-2.5, MS116-20.0, MS116-25.0, MS116-32.0, MS116-4.00, MS116-6.3

Open type, Manual motor controllers, suitable for group installation, suitable as motor disconnect, suitable as tap conductor protection, provided with overload protection (starter) Model(s) MS165 or MO165 followed by -16, -20, -25, -32, -42, -54, or -65.

# - May be followed by L.

[Last Updated](#) on 2015-02-11

[Questions?](#)

[Print this page](#)

[Terms of Use](#)

[Page Top](#)

© 2015 UL LLC

When the UL Leaf Mark is on the product, or when the word "Environment" is included in the UL Mark, please search the [UL Environment database](#) for additional information regarding this product's certification.

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2015 UL LLC".