

LINE CARD


ReliaGear® XFMR

low voltage dry type transformers

Reliable inventory, competitive price, fast delivery



Available in some areas: Enter a stock transformer order today, receive it tomorrow. No additional charge. Ask your ABB Account Manager today for details.



FastShip
Transformers



3-phase vented

- 15–750 kVA, DOE efficiency
- General purpose
- K-factor
- Low temperature rise
- Low noise
- Electronic noise isolation
- Harmonic mitigating
- Drive isolation (DIT)
- Stainless steel enclosure available



Control power

- Single-phase
- Fully encapsulated
- Terminal block or leads out
- 0.05–3 kVA



1-phase vented

- 15–100 kVA, DOE efficiency
- General purpose
- Low temperature rise



Enclosed and encapsulated

- Single-phase
- 0.05–15 kVA
- NEMA 3R



Totally enclosed, non-ventilated

- Three-phase 15–75 kVA
- TP-1 efficiency
- Aluminum or copper coil
- NEMA 3R



Buck boost

- Single-phase
- 0.05–3 kVA
- NEMA 3R



Midtapped

- Three-phase, DOE efficiency
- 15–500 kVA
- Aluminum or copper coil



Servicenter™ integrated transformer and distribution panel

- Aluminum or copper coil
- Single-phase, 5–25 kVA
 - Copper coil
- Three-phase, 15–30 kVA
 - Aluminum or copper coil
- NEMA 3R

ReliaGear® XFMR

Our most popular transformer categories

3-phase vented

- 480 V primary — 208Y/120 V secondary
- Aluminum, 150 °C rise, NEMA 2, DOE efficiency

KVA	Product number
15	9T10A1001
30	9T10A1002
45	9T10A1003
75	9T10A1004
112.5	9T10A1005
150	9T10A1006
225	9T10A1007
300	9T10A1008
500	9T10A1009
750	9T10A1302



- Rain shield kits are stocked, sold separately
- Wall-mount brackets are stocked, sold separately
- Lug kit and ground bar kit included on most units up through 150 kVA

1-phase vented

- 240x480 V primary — 120/240 V secondary
- Aluminum, 150 °C rise, NEMA 2, DOE efficiency

KVA	Product number
15	9T33A2670
25	9T33A2671
37.5	9T33A2672
50	9T33A2673
75	9T33A2674
100	9T33A2675



- Rain shield kits are stocked, sold separately
- Lug kit and ground bar are included, installed
- Wall-mount brackets are stocked, sold separately

1-phase enclosed and encapsulated

- 240x480 V primary — 120/240 V secondary
- Copper, 100 °C rise, NEMA 3R, 60 Hz

KVA	Product number
0.50	9T51B0008
0.75	9T51B0009
1.0	9T51B0010
1.5	9T51B0011
2.0	9T51B0012



ABB Inc.
305 Gregson Drive
Cary, NC 27511

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB Inc. does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

electrification.us.abb.com

Control power

- Single-phase
- 220x440, 230x460, 240x480 V primary — 110, 115, 120 V secondary
- Copper, 55 °C rise, NEMA 3R

KVA	Product number
0.05	9T58K0042
0.08	9T58K0043
0.10	9T58K0044
0.15	9T58K0045
0.20	9T58K0046
0.25	9T58K0047
0.30	9T58K0048
0.38	9T58K0049
0.50	9T58K0050



Buck boost

- Single-phase
- 120/240 V primary — 12/24 V secondary
- Copper, 55 °C rise, NEMA 3R

KVA	Product number
0.05	9T51B0102
0.075	9T51B0103
0.10	9T51B0104
0.15	9T51B0105
0.25	9T51B0107
0.50	9T51B0108
0.75	9T51B0109
1.0	9T51B0110
1.5	9T51B0111
2.0	9T51B0112
3.0	9T51B0113



1-phase enclosed and encapsulated

- 240x480 V primary — 120/240 V secondary
- Aluminum, 115 °C rise, NEMA 3R, 60 Hz

KVA	Product number
5	9T21B1004G02
7.5	9T21B1005G02
10	9T21B1006G02
15	9T21B9103



We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB Inc. Copyright© 2024 ABB All rights reserved