


On-load tap-changer type UCGR./C, VUCGR./C, 21 tap positions, plus/minus switching.
 Max. effective No. of turns in pos. 1.
 The tap-changer is delivered set in pos. 11, the preceding pos. was 11A.

Lindningskopplare typ UCGR./C, VUCGR./C, 21 lägen, plus/minus koppling.
 Max antal effektiva varv i läge 1.
 Lindningskopplaren levereras inställd i läge 11, föregående läge var 11A.



Pos. Läge	R connects in direction R förbinder i riktning	Tap selector and diverter switch connect Väljaren och lastkopplaren förbinder	
1	↓	1-V-x	
2		2-H-v	
3		3-V-x	
4		4-H-v	
5		5-V-x	
6		20-21	6-H-v
7		20-21	7-V-x
8		↑	8-H-v
9		↑	9-V-x
10		↑	10-H-v
11A		↓	11-V-x
11	↓	12-H-v	
11B	↑	1-V-x	
12	↑	2-H-v	
13	↑	3-V-x	
14	↑	4-H-v	
15	↑	5-V-x	
16	20-22	6-H-v	
17	20-22	7-V-x	
18	↑	8-H-v	
19	↑	9-V-x	
20	↑	10-H-v	
21	↓	11-V-x	

A position with letter is a through position and gives the same voltage as the normal position.

Läge med bokstav är genomloppsläge och ger samma spänning som normalläget.

The tap-changer is shown in pos. 11, the preceding pos. was 11A.
 The tap selector and the change-over selector are seen from above.
 Contact arm V is located above contact arm H.

Lindningskopplaren visad i läge 11, föregående läge var 11A.
 Väljaren och plus/minus-omkopplaren sedda uppifrån.
 Kontaktarm V ligger över kontaktarm H.

Continuous lines show leads included in the tap-changer. Dashed lines show leads belonging to the cleats and leads.

Heldragna linjer visar ledare som ingår i lindningskopplaren. Streckade linjer visar ledare som tillhör anslutningsdonet.

Sheet	Cont		Year		Week		
	Cont		Year		Week		
Form No.	Cont		Year		Week		
	Cont		Year		Week		
1		VUCG Added.		TOLA		07 47	
Rev Ind		Revision		Appd		Year Week	
Accepted by qual control		Accepted for prod by		Description (English)		DATAORIGINAL	
R.Yngvesson				CONNECTION DIAGRAM			
Design checked by		Drawn by		Description (own language)		File name	
B-O.Stenestam		L.Bergman		KOPPLINGSSHEMA		0374-6	
Drawing checked by		Issued by Dept		Year		Sheet	
M.Hedlund		COM/TKO		97 17		1	
ABB		Asea Brown Boveri		5492 0374-6		RevInd	
						Cont	
						-	

We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden. © ABB 19