



Ref. Certif. No.

SE-96557M3

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Contactor

Name and address of the applicant

ABB France
11 Rue d'Arsonval
69680 Chassieu
FRANCE

Name and address of the manufacturer

Same as applicant

Name and address of the factory

Additional Information on page 2

Note: When more than one factory, please report on page 2

Ratings and principal characteristics

U_e = 220-240 / 380-415 / 440 / 500 / 690 / 1000VAC;
I_e = 25A - 130A; I_q = 35kA (1000V) or 80kA (690V, 3-pole)
or 100 kA (220-440 / 500V);
U_i = 1000V; U_{imp}=8kV

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

-

Model / Type Ref.

AF*80*-30-**-**, AF*96*-30-**-**, AF*80*-40-**-**,
AF*80*-22-**-**

Additional information (if necessary may also be reported on page 2)

Additional Information on page 2-3

A sample of the product was tested and found to be in conformity with

IEC 60947-4-1:2018

As shown in the Test Report Ref. No. which forms part of this Certificate

2300599STO-001

This CB Test Certificate is issued by the National Certification Body

Intertek Semko AB
Torshamnsgatan 43
Box 1103
SE-164 22 Kista, Sweden

Date: 03 May, 2023

intertek

Signature:

Henrik Wikström



Ref. Certif. No.

SE-96557M3

Factories

ABB France
11 Rue d'Arsonval,
69680 Chassieu
FRANCE

ABB Xinhui Low Voltage Switchgear Company Ltd
Jinguzhou Industrial Development Zone
Xinhui District, Jiangmen City
Guangdong Province CN-529100
CHINA

Additional information

Rated conditional short-circuit current, $I_q = 35\text{kA}$ (1000V) or 80kA (690V, 3-pole) or 100 kA (220-440 / 500V)

Rated insulation voltage, $U_i = 1000\text{V}$

Rated impulse withstand voltage, $U_{imp}=8\text{kV}$

Type	AC-1: 1000V	AC-1: 690V	AC-3: 220- 440V	AC-3: 500V	AC-3: 690V	AC-3: 1000V	AC-3e 220- 440V	AC-3e 500V	AC-3e 690V	AC-4: 220- 500V	AC-4: 690V	AC-8a: 400V
AF80-30 (I_n):	50	125	80	65	49	25	80	65	49	65*	40	105
AF96-30 (I_n):	60	130	105	80	57	30	105	80	57	76*	45	120
AF80-40 (I_n):	50	125	80	65	49	25	-	-	-	65	40	-
AF80-22 (I_n):	50	125	80	65	49	25	-	-	-	65	40	-

*Also includes reversing starter contactor

Date: 03 May, 2023

Signature: 

Explanation of type designation AF*80*-30-**-**, AF*96*-30-**-**, AF*80*-40-**-**, AF*80*-22-**-**:

AF S 80 - B - 30 - 11 - 13
1 2 3 4 5 6 7

1 = Main designation

AF Contactor AF Range

2 = Application

"blank": standard application

S: contactor for safety application

3 = Size of contactor

80, 96

4 = Type of material

"blank" = Standard material

B = Contactor for railway applications (special raw plastic)

5 = Number of main contacts

30 = 3 NO- and 0 NC-contacts

22 = 2 NO- and 2 NC-contacts

40 = 4 NO- and 0 NC-contacts

6 = Number of auxiliary contacts

00 = 0 NO- and 0 NC-contacts.

04 = 0 NO- and 4 NC-contacts. Mounted as 2nd stack, (only for AFS)

11 = 1 NO- and 1 NC-contacts. Side mounting

13 = 1 NO- and 3 NC-contacts. Mounted as 2nd stack, (only for AFS)

22 = 2 NO- and 2 NC-contacts. Mounted as 2nd stack

31 = 3 NO- and 1 NC-contacts. Mounted as 2nd stack, (only for AFS)

7 = Coil configuration

11 = 20-60VDC/24-60VAC

12 = 48-130VAC/VDC

13 = 100-250VAC/VDC

14 = 250-500VAC/VDC

41 = 24-60VAC

This certificate replaces CB certificate SE-96557M2, dated 27 September 2020. A new certificate is issued due to new models intended for railway applications.

Date: 03 May, 2023

Signature: 