

# TropOS 6420

## Outdoor mesh core router



The TropOS 6420 outdoor mesh router is a cost-effective, easy to deploy, high-performance outdoor networking solution.

TropOS 6420 provides superior reliability by accessing 653 MHz of RF spectrum (463 MHz in ETSI) using automatic interference avoidance capabilities of TropOS Mesh OS. The TropOS 6420 uses the 802.11a/b/g/n wireless standards to deliver 600 Mbps total wireless data rate, 300 Mbps at 2.4 GHz and another 300 Mbps at 5 GHz.

### Wireless

- IEEE 802.11b/g/n radio
  - Modulation: 802.11g/n - OFDM (64-QAM, 16-QAM, QPSK, BPSK); 802.11b - DSSS (DBPSK, DQPSK, CCK)
  - Media access protocol: CSMA/CA with ACK
  - TX power (dBm EIRP)

Band (MHz)	FCC	ETSI	Brazil
2400-2473	21-36	N/A	N/A
2400-2483	N/A	5-20	11-26

assumes use of 7.4 dBi antennas

- 2x2 MIMO-antenna system: 2-TX x 2-RX
- 7 dBi integrated omnidirectional antennas
- RX Sensitivity:
  - 98 dBm @ 1 Mbps
  - 96 dBm @ 6 Mbps
- IEEE 802.11a/n radio
  - Modulation: 802.11a/n - OFDM (64-QAM, 16-QAM, QPSK, BPSK)
  - Media access protocol: CSMA/CA with ACK
  - TX Power (dBm EIRP)

Band (MHz)	FCC	ETSI	Brazil
5150-5250	21-36	N/A	N/A
5250-5350	15-30	N/A	N/A
5470-5725	15-30	15-30	N/A
5725-5850	21-36	21-36	15-30

assumes use of 8 dBi antennas

- 2x2 MIMO-antenna system: 2-TX x 2-RX
- 8 dBi integrated omnidirectional antennas
- RX sensitivity:
  - 95 dBm @ 6 Mbps
- Support for 802.11n MIMO
- Integrated GPS receiver

### Interfaces

- Full 802.11a/b/g/n wireless, 802.11n client compatibility
- One IEEE 802.3u autosensing 10/100/1000BASE-T Ethernet port
- One IEEE 802.3u autosensing 10/100BASE-T Ethernet port or one serial port, RS-232 and/or RS-485
- Protocols: DNP3, Modbus (RTU), Modbus (ASCII), raw (serial pass-through) support
- IPv4, IPv6-ready
- BGP
- 802.1q VLAN support (ESSID and IP based tagging)
- Support for static and dynamic addressing for wireless and wired clients
- Session-persistent mobility across subnets
- IP multicast forwarding, IGMPv3; IGMP Proxy
- Automatic rate, power, channel and band control
- IEC 61850 GOOSE messaging
- Reliable broadcast
- Network Address Translation (NAT) support for wired clients

### Quality of service

- 802.11e 802.11e WMM
- 802.1p/q with 4 queues per VLAN and ESSID
- 802.1p and DSCP
- VoIP and VoWiFi support

### Management

- Local and remote management tools via HTTPS
- Role-based authentication (4 levels)
- Configuration save and restore
- Over the air software upgrades
- SNMP (standard MIBs)
- Wireless, network and client monitoring and statistics
- Infrared (IR) port
- Wireless rescue
- SuprOS carrier-class NMS support

### Security

- IPsec VPNs with tunnels to wired client interfaces using AES
- Authentication: WPA, WPA2, 802.11i, RADIUS, 802.1x (includes EAP-TLS, EAP-TTLS, EAP-SIM, PEAP)
- Encryption: open, WEP, TKIP, AES-CCM
- AES encryption of mesh and control traffic
- Technical controls required to achieve NERC CIP v5 compliance
- Multiple BSSIDs & ESSIDs (ESSID suppression)
- Integrated firewall
  - Packet filtering on TCP/UDP port, protocol, SA, DA
  - Peer-to-peer blocking
  - Client access control lists
- Evil twin detection and reporting
- Denial of service (DoS) attack detection and reporting
- Jamming attack detection and reporting

### Environmental specifications

- Operating temperature range: -40°C to 75°C
- Storage temperature range: -40°C to 85°C
- Weather rating: IP67 UL579/IEC 60529 IP67
- Wind survivability: >165 mph
- Wind loading (165 mph): <210 Newtons
- ASTM B117 salt fog rust resistance compliant
- Shock & vibration: ETSI 300-19-2-4 spec T4.1E class 4M3
- Transportation: ISTA 2A

### Power

- 802.3at on the 10/100/1000BASE-T port
- 12-48 VDC on the 100/100BASE-T port
- 120/240 VAC with optional, external accessory (optional external battery backup available)
- Power consumption: 4 W typical
- Power-on and network status LEDs

### Physical

- Dimensions (w/o mounting brackets): 8.75" (22.2 cm) x 7.25" (18.4 cm) x 14" (35.6 cm) high with antennas
- Weight: 5 lbs (2.3 kg) max., without mounting brackets
- Outdoor pole mounting kit and cable glands included with each unit

### Wireless approvals

- FCC CFR 47 Part 15
- Industry Canada RSS 210
- EN 301 489-17
- EN 300 328
- EN 301 893
- EN 302 502

### Safety approvals

- EN 60950
- IEC 950
- UL 60950-1
- CSA 22.2 No. 60950-1
- UL 579/IEC 60529 IP67 rated for outdoor use
- UL 1449/IEC 60664-1
- CE
- IEEE 1613

### Protection

- Antenna protection integrated
- Electrical protection:
  - EN61000-4-4 Level 2 electrical fast transient burst immunity
  - EN61000-4-3 Level 2 EMC field immunity
  - EN61000-4-2 Level 2 (contact), Level 3 (air) ESD immunity

### Warranty

- Five (5) year hardware warranty
- Software and hardware maintenance plans available

Click the link to find out more information about our [wireless mesh routers](#).