

# Stanilite®

## Platinum exit LED Quickfit® weatherproof Nexus®



### Range

Platinum range

### Product group


Exit LED Quickfit



### Features



- 5 year warranty
- LED technology 100,000 hours plus lamp life
- Low power consumption and LED light source for reduced operation and maintenance costs
- IP65 weatherproof enclosure
- Advanced charging technology combined with Lithium iron phosphate battery for long life and low maintenance
- Nexus monitored, either cabled or wireless
- Quickfit unique steel slide connect bracket for quick installation and easy maintenance
- UV stabilised vandal resistant polycarbonate cover or high impact chemical resistant acrylic cover option
- Can be wall or ceiling mounted and optional bracket kits available for strengthened wall and cantilever mounting
- Not suitable for installations where exposure to direct sunlight may occur



Catalogue no.	Description
<b>Nexus products</b>	
PWQFNXSLEDP-1P	Platinum exit LED Quickfit weatherproof Nexus LX single sided polycarbonate picto
PWQFNXSLEDP-2P	Platinum exit LED Quickfit weatherproof Nexus LX single sided polycarbonate <picto
PWQFNXSLEDP-3P	Platinum exit LED Quickfit weatherproof Nexus LX single sided polycarbonate picto>
PWQFNXSLEDP-5P	Platinum exit LED Quickfit weatherproof Nexus LX double sided polycarbonate picto
PWQFNXSLEDP-6P	Platinum exit LED Quickfit weatherproof Nexus LX double sided polycarbonate picto AOW
PWQFNXSLEDA-1P	Platinum exit LED Quickfit weatherproof Nexus LX single sided acrylic picto
PWQFNXSLEDA-2P	Platinum exit LED Quickfit weatherproof Nexus LX single sided acrylic <picto
PWQFNXSLEDA-3P	Platinum exit LED Quickfit weatherproof Nexus LX single sided acrylic picto>
PWQFNXSLEDA-5P	Platinum exit LED Quickfit weatherproof Nexus LX double sided acrylic picto
PWQFNXSLEDA-6P	Platinum exit LED Quickfit weatherproof Nexus LX double sided acrylic picto AOW
PWQFNRFLEDP-1P	Platinum exit LED Quickfit weatherproof Nexus RF single sided polycarbonate picto
PWQFNRFLEDP-2P	Platinum exit LED Quickfit weatherproof Nexus RF single sided polycarbonate <picto
PWQFNRFLEDP-3P	Platinum exit LED Quickfit weatherproof Nexus RF single sided polycarbonate picto>
PWQFNRFLEDP-5P	Platinum exit LED Quickfit weatherproof Nexus RF double sided polycarbonate picto
PWQFNRFLEDP-6P	Platinum exit LED Quickfit weatherproof Nexus RF double sided polycarbonate picto AOW
PWQFNRFLEDA-1P	Platinum exit LED Quickfit weatherproof Nexus RF single sided acrylic picto
PWQFNRFLEDA-2P	Platinum exit LED Quickfit weatherproof Nexus RF single sided acrylic <picto
PWQFNRFLEDA-3P	Platinum exit LED Quickfit weatherproof Nexus RF single sided acrylic picto>
PWQFNRFLEDA-5P	Platinum exit LED Quickfit weatherproof Nexus RF double sided acrylic picto
PWQFNRFLEDA-6P	Platinum exit LED Quickfit weatherproof Nexus RF double sided acrylic picto AOW

### Accessories

WQFCLH	Cantilever mounting bracket - heavy duty
WQFCLL	Cantilever mounting bracket - light duty
WQFWM	Wall mount bracket
29-PIQFVERT	Quickfit pictograph vertical insert pack 4 piece set *

Note: \* Refer to the installation manual for vertical installation requirements

### Spare parts

03-01302P	Battery LiFePO4 3.2V 3.2Ah
-----------	----------------------------

<b>Dimensions</b>			
	<b>Length</b>	<b>Width</b>	<b>Height</b>
	466mm	155mm	274mm
<b>Weight</b>			
	<b>Model</b>	<b>Weight</b>	
	Nexus LX/RF	3.6kg	
<b>Construction</b>			
	<b>Part</b>	<b>Construction</b>	
	Body	Black UV/FR polycarbonate	
	Diffuser	Opal acrylic	
	Bracket	Black powder coated zinc steel	
	Enclosure cover	UV polycarbonate or high impact acrylic	
	Enclosure base	Black glass reinforced UV stabilised nylon	
<b>Light source</b>			
	<b>Model</b>	<b>Light source</b>	
	Nexus LX/RF	Multiple LED 1.6W	
<b>Power consumption</b>			
	<b>Model</b>	<b>Power consumption</b>	
	Nexus LX/RF	3.2W	
<b>Photometrics</b>			
	<b>Model</b>	<b>Class</b>	<b>Classification</b>
	Nexus LX/RF	C0	D3.2
		C90	D3.2

Note: Preliminary results

Note:

- Designed to comply with AS2293 and meet relevant Australian EMC standards