

COVER PAGE FOR TEST REPORT

Test Item Description:	Redundancy Unit
Model/Type Reference:	CP-A RU
Rating(s):	Input I: 10 - 40 Vdc, 1 - 20 A Input II: 10 - 40 Vdc, 1 - 20 A
	Output: Input -0.6 V, 1 - 40 A
Standards:	IEC 60950-1:2001, First Edition
Applicant Name and Address:	ABB STOTZ-KONTAKT GMBH HAUPTSTRASSE 14-16 78132 HORNBERG GERMANY
Factory Location(s):	ABB STOTZ-KONTAKT GMBH HAUPTSTRASSE 14-16 78132 HORNBERG GERMANY ABB XINHUI LOW VOLTAGE SWITCHGEAR CO LTD JINGUZHOU INDUSTRIAL DEVELOPMENT ZONE XINHUI GUANGDONG CHINA
This Report includes the following parts, in addition to this cover page:	
<ol style="list-style-type: none">1. Specific Technical Criteria2. Clause Verdicts3. Critical Components4. Test Results5. Enclosures<ol style="list-style-type: none">a. National Differencesb. Photographsc. Manualsd. Miscellaneous	
<p>All applicable tests according to the above standard(s) have been carried out. Test results are valid only for the tested equipment. This Test Report can be reproduced only in whole. Amendments and corrections can be reproduced only with the original CB Test Report. Written permission from UL International Demko A/S is required if the test report is copied in part.</p>	

	Test Report issued under the responsibility of: UL International Demko A/S	
TEST REPORT IEC 60950-1, First Edition Information technology equipment-Safety Part 1: General Requirements		
Report Reference No: E196145-A7-CB-1 Date of issue: 2008-06-12 Total number of pages: 39		
CB Testing Laboratory: UL International (Netherlands) B.V. Address: Delta 1A, Building L'Aimant, Business Park IJsseloord 2, 6825 ML Arnhem, The Netherlands		
Applicant's name: ABB STOTZ-KONTAKT GMBH Address: HAUPTSTRASSE 14-16 78132 HORNBERG GERMANY		
Test specification: Standard: IEC 60950-1:2001, First Edition Test procedure: CB Scheme Non-standard test method: N/A		
Test Report Form No.: IEC60950_1B Test Report Form originator: SGS Fimko Ltd Master TRF: dated 2003-03		
<p>Copyright © 2005 IEC System for Conformity Testing and Certification of Electrical Equipment (IECEE), Geneva, Switzerland. All rights reserved.</p> <p>This publication may be reproduced in whole or in part for non-commercial purposes as long as the IECEE is acknowledged as copyright owner and source of the material. IECEE takes no responsibility for and will not assume liability for damages resulting from the reader's interpretation of the reproduced material due to its placement and context.</p> <p>If this test Report is used by non-IECEE members, the IECEE/IEC logo shall be removed.</p> <p>This report is not valid as a CB Test Report unless signed by an approved CB Testing Laboratory and appended to a CB Test Certificate issued by an NCB in accordance with IECEE 02.</p>		

Test item description	Redundancy Unit
Trade Mark	ABB STOTZ-KONTAKT GmbH
	
Model/Type reference	CP-A RU
Manufacturer	ABB STOTZ-KONTAKT GMBH HAUPTSTRASSE 14-16 78132 HORNBERG GERMANY
Rating	Input I: 10 - 40 Vdc, 1 - 20 A Input II: 10 - 40 Vdc, 1 - 20 A Output: Input -0.6 V, 1 - 40 A