


We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden.  
© ABB '19

On-load tap-changer type (V)UCGL./F, (V)UCLL./F, UCCL./F  
14 positions, linear switching.  
Min. effective No. of turns in pos. 1.  
The tap-changer is delivered set in pos. 8,  
the preceding pos. was 7.

Lindningskopplare typ (V)UCGL./F, (V)UCLL./F, UCCL./F  
14 lägen, linjär koppling.  
Min antal effektiva varv i läge 1.  
Lindningskopplaren levereras inställd i läge 8,  
föregående läge var 7.



Pos. Läge	Tap selector and diverter switch connect	
1	1-V-x	30
2	2-H-v	
3	3-V-x	
4	4-H-v	
5	5-V-x	
6	6-H-v	
7	7-V-x	
8	8-H-v	
9	9-V-x	
10	10-H-v	
11	11-V-x	
12	12-H-v	
13	13-V-x	
14	14-H-v	

The tap-changer is shown in pos. 8,  
the preceding pos. was 7.  
The tap selector is seen from above.  
Contact arm V is located above contact arm H.

Lindningskopplaren visad i läge 8,  
föregående läge var 7.  
Väljaren sedd uppifrån.  
Kontaktarm V ligger över kontaktarm H.

Continuous lines show leads included in the  
tap-changer. Dashed lines show leads belonging  
to the cleats and leads.

Heldragna linjer visar ledare som ingår i  
lindningskopplaren. Streckade linjer visar  
ledare som tillhör anslutningsdonet.

Sheet	Cont										
	Year	Week	Dept								
Form No.	Design checked by			Rev Ind	Revision	Appd	Year	Week			
	Drawn by			Accepted by qual control		Accepted for prod by		Description (English)		DATAORIGINAL	
Design checked by			Design checked by		Drawn by		Description (own language)		File name		
Drawn by			H.Sundberg		A.Wang		KOPPLINGSSHEMA				
Design checked by			N.Gustavsson		Issued by Dept		Year	Week			
				CO/TK		14	02	1ZSC004308-AAK		Lang	Sheet
										1	Cont
										-	