



Number	Part	Weight [kg]
1	Steering module	8000
2	Propulsion Module (excl. propeller)	16000 (S) / 17000 (L)
3	Propeller	1300 (min) - 1900 (max)
4	Steering drive	500 / unit

Prepared	Separate part list with separate No. <input type="checkbox"/>	Title	Scale
Reviewed	Responsible department	MAIN DIMENSIONS	1:50
Approved	Original dwg		
Distribution	Functional code AH	Order No.	Language EN
		Weight	Size A2
		Type AZIPOD C00980-S1800E2	Revision A
		Document No. 3AFV6040408	Sheet 1/1
ABB Marine & Turbocharging, Helsinki			AutoCAD

We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without the prior written consent of ABB Oy, Marine & Turbocharging, Propulsion Units.

General tolerances for linear and angular dimensions and geometrical tolerances: ISO 2768 -mK Referential standards BADA 422, DIN 71681.1

Symbols for roughness according to ISO 1302, 9A0A 431