


On-load tap-changer type UBBL, 14 tap positions, linear switching.
 Min effective No. of turns in pos 1.
 The tap-changer is delivered set in pos 7.

Lindningskopplare typ UBBL, 14 lägen, linjär-koppling.
 Min antal effektiva varv i läge 1.
 Lindningskopplaren levereras inställd i läge 7.

Pos Läge	H connects förbinder
1	14 - 15
2	13 - 15
3	12 - 15
4	11 - 15
5	10 - 15
6	9 - 15
7	8 - 15
8	7 - 15
9	6 - 15
10	5 - 15
11	4 - 15
12	3 - 15
13	2 - 15
14	1 - 15

We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden.
 © ABB 19



H Main contact
Huvudkontakt
M1, M2 Transition contacts
Motståndskontakter

1) OUTPUT TERMINAL
STRÖMAVTAGNING

1) Internal connections between the terminals 15 of the three phases are included in the star-point type. Dashed lines show leads belonging to the cleats and leads.

Inre förbindningar mellan uttag 15 i de tre faserna ingår i nollpunktsutförande. Streckade linjer visar ledare som tillhör anslutningsdonet.

1	Selector switch changed position.	SK	08	36
Rev Ind	Revision	Appd	Year	Week

Accepted by qual control R.Yngvesson	Accepted for prod by	Description (English) CONNECTION DIAGRAM UBBL	DATAORIGINAL
Design checked by B-O.Stenestam	Drawn by L.Bergman	Description (own language) KOPPLINGSSCHEMA UBBL	File name 0390-10
Drawing checked by M.Hedlund	Issued by Dept Year Week COM/TKO 97 32	Lang Sheet 1	
ABB Asea Brown Boveri		5492 0390-10	
Rev Ind	Cont	-	