

TECHNICAL DATA

# ABB i-bus® KNX

## HCC/S 2.2.1.1

### Heating/cooling circuit controller



—

### Device description

The device is a modular installation device (MDRC) in *proM* design. It is designed for installation in electrical distribution boards and small housings with a 35 mm mounting rail (to EN 60715).

The device is KNX-certified and can be used as a product in a KNX system → EU declaration of conformity.

The device is powered via the bus (ABB i-bus® KNX) and requires no additional auxiliary voltage supply. The connection to the bus is made via a bus connection terminal on the front of the housing. The loads are connected to the outputs using screw terminals → terminal designation on the housing.

The software application Engineering Tool Software (ETS) is used for physical address assignment and parameterization.

—

## Device functions

The following functions for each channel are available for activating heating/cooling circuits:

- Controller channel
- Actuator channel

The two device channels are independent of each other. It is possible to control two different rooms. As an alternative, it is also possible to activate a double pump by combining both channels (channel bundling).

### Controller channel

The internal controller is activated in the function as a controller channel. The controller is used to process the data received at the inputs (actual values) or via the bus (ABB i-bus® KNX) (actual values and setpoints). The control values are calculated from the data received and transmitted to the outputs.

### Actuator channel

The internal controller is deactivated in the function as an actuator channel. The control values for activating the outputs are calculated by an external controller and received via the bus (ABB i-bus® KNX).

## Connections

The devices possess the following connections:

- 10 inputs for sensors
- 2 valve outputs for activating analog and motor-driven valve drives
- 2 pump outputs
- 1 bus connection

The tables below provide an overview of the maximum number of devices that can be connected to the individual product variants.

### Valve outputs

	HCC/S 2.1.X.1	HCC/S 2.2.X.1
Analog valve drives (0 ... 10 V)	2	
Motor-driven valve drives (3-point)		2

### Pump outputs

	HCC/S 2.1.X.1	HCC/S 2.2.X.1
Pumps, 1-phase	2	2
Double pump, 1-phase	1	1

### Physical inputs

	HCC/S 2.1.X.1	HCC/S 2.2.X.1
Binary sensors (floating)	6	6
Temperature sensors	4	4

## Inputs

Function	a	b	c	d	e	f	g	h	i	j
Temperature sensor										
PT100	x	x				x	x			
PT1000	x	x				x	x			
KT/KTY	x	x				x	x			
KT/KTY user-defined	x	x				x	x			
NTC10k	x	x				x	x			
NTC20k	x	x				x	x			
NI-1000	x	x				x	x			
Binary sensor (floating)			x	x	x			x	x	x
Pump status (floating contact)			x					x		
Pump fault (floating contact)				x					x	
Pump repair switch (floating contact)					x					x

## Outputs

### Valve outputs


#### HCC/S 2.2.X.1

Function	A	B
Motor-driven valve drive (3-point)	open	close
Fault detection (overload/short circuit)	x	x
Automatic closing if pump shut down	x	x

—  
**Pump outputs**


<b>Function</b>	<b>A</b>	<b>B</b>
<b>Individual pump</b>		
Automatic operation	x	x
Direct operation	x	x
Automatic switch off on fault	x	x
<b>Double pump</b>		
Automatic operation	x	
Direct operation	x	
Automatic switch off on fault	x	
Automatic weekly change	x	
Automatic change on fault	x	

—  
Dimension drawing



2CDC07202F0017

—  
**Connection diagram**




—  
**Legend**

- |                               |                                |
|-------------------------------|--------------------------------|
| 1 Label carriers              | 8 Binary input channel A       |
| 2 <i>Programming</i> LED      | 9 Valve output channel A       |
| 3 <i>Programming</i> button   | 10 Pump output channel B       |
| 4 Bus connection terminal     | 11 Temperature input channel B |
| 5 Cover cap                   | 12 Binary input channel B      |
| 6 Pump output channel A       | 13 Valve output channel B      |
| 7 Temperature input channel A |                                |

2CDC072035F0017

—  
**Operating and display elements**

Operating control/LED	Description/function	Display
	Assignment of the physical address	LED On: Device in programming mode
<i>Programming button/LED</i>		



## General technical data

<b>Device</b>	Dimensions	90 × 140 × 63.5 mm (H x W x D)
	Mounting width in space units	8 modules, 17.5 mm each
	Weight	0.24 kg
	Mounting position	Any
	Mounting variant	35 mm mounting rail
	Design	ProM
	Degree of protection	IP 20
	Protection class	II
	Overtoltage category	III
	Pollution degree	2
<b>Materials</b>	Housing	Polycarbonate, Makrolon FR6002, halogen free
<b>Material note</b>	Fire classification	Flammability V-0
<b>Electronics</b>	Rated voltage, bus	30 V DC
	Voltage range, bus	21 ... 32 V DC
	Current consumption, bus	< 12 mA
	Power loss, device	≤ 3 W
	Power loss, bus	≤ 0.25 W
	Power loss, relay output 5 A	≤ 0.6 W
	KNX safety extra low voltage	SELV
<b>Connections</b>	Connection type, KNX bus	Plug-in terminal
	Cable diameter, KNX bus	0.6 ... 0.8 mm, solid
	Connection type, inputs/outputs	Screw terminal with universal head (PZ 1)
	Pitch	6.35 mm
	Tightening torque, screw terminals	0.5 ... 0.6 Nm
	Conductor cross-section, flexible	1 × (0.2 ... 2.5 mm <sup>2</sup> ) / 2 × (0.2 ... 2.5 mm <sup>2</sup> )
	Conductor cross section, rigid	1 × (0.2 ... 4 mm <sup>2</sup> ) / 2 × (0.2 ... 4 mm <sup>2</sup> )
	Conductor cross section with wire end ferrule without plastic sleeve	1 × (0.25 ... 2.5 mm <sup>2</sup> )
	Conductor cross section with wire end ferrule with plastic sleeve	1 × (0.25 ... 4 mm <sup>2</sup> )
Conductor cross section with TWIN wire end ferrule	1 × (0.5 ... 2.5 mm <sup>2</sup> )	
Length, wire end ferrule contact pin	≥ 10 mm	
<b>Certificates and declarations</b>	Declaration of conformity CE	→ 2CDK508232D2701
<b>Ambient conditions</b>	Operation	-5 ... +45 °C
	Transport	-25 ... +70 °C
	Storage	-25 ... +55 °C
	Humidity	≤ 95 %
	Condensation allowed	No
	Atmospheric pressure	≥ 80 kPa (corresponds to air pressure at 2,000 m above sea level)

## Inputs - contact scanning

<b>Rated values</b>	Number of inputs	6
<b>Contact scanning</b>	Scanning current	≤ 1 mA
	Scanning voltage	≤ 12 V DC
<b>Cable length</b>	Between sensor and device input, one-way	≤ 100 m

## Inputs - temperature sensor

<b>Rated values</b>	Number of inputs	4
<b>Resistance</b>	Selection	User-defined
	PT 1.000	2-conductor technology
	PT100	2-conductor technology
	KT	1k
	KTY	2k
	NI	1k
	NTC	10k, 20k
<b>Cable length</b>	Between sensor and device input, one-way	≤ 100 m

## Valve outputs – motor-driven

Rated values	Number of outputs	2
	Non-floating	Yes
	Rated voltage $U_n$	230 V AC
	Voltage range	24 ... 230 V AC
	Rated frequency	50/60 Hz
	Rated current $I_n$	0.5 A
	Continuous current at $T_u$ Up to 20 °C	0.25 A resistive load per channel
	Continuous current at $T_u$ Up to 45 °C	0.15 A resistive load per channel
	Inrush current at $T_u$ Up to 45 °C	≤ 1.6 A (for 10 s)
		$T_u$ = Ambient temperature
	Minimum load (per output)	1.2 VA

## Pump outputs – relays 5 A

Rated values	Number of outputs	2
	Rated voltage $U_n$	250 V AC
	Rated current $I_n$ (per output)	5 A
	Rated frequency	50/60 Hz
	Back-up protection	≤ 6 A
	Relay type	Bi-stable
Switching currents	AC-1 operation ( $\cos \varphi = 0.8$ )	≤ 5 A
	AC-3 operation ( $\cos \varphi = 0.45$ )	≤ 5 A
	Switching current at 5 V AC	≥ 0.02 A
	Switching current at 12 V AC	≥ 0.01 A
	Switching current at 24 V AC	≥ 0.07 A
Service life	Mechanical service life	≥ 10 <sup>7</sup> switching operations
	AC-1 operation ( $\cos \varphi = 0.8$ )	≥ 10 <sup>6</sup> switching operations
	AC-3 operation ( $\cos \varphi = 0.45$ )	≥ 10 <sup>6</sup> switching operations
Switching operations	Switching operations per minute when one relay switches	≤ 500

## Device type

Device type	Heating/cooling circuit controller	HCC/S 2.2.1.1
	Application	Heating/Cooling Circuit Controller, 3-point, 2f/ ... ... = current version number of the application
	Maximum number of group objects	106
	Maximum number of group addresses	255
	Maximum number of assignments	255

### Note

Observe software information on the website  
→ [www.abb.com/knx](http://www.abb.com/knx).

—  
**Ordering details**

Description	MW	Type	Order no.	Packaging [pcs.]	Weight (incl. packaging) [kg]
Heating/cooling circuit controller	8	HCC/S 2.2.1.1	2CDG110220R0011	1	0.29



---

**ABB STOTZ-KONTAKT GmbH**

Eppelheimer Straße 82

69123 Heidelberg, Germany

Tel.: +49 (0)6221 701 607

Fax: +49 (0)6221 701 724

Email: [knx.marketing@de.abb.com](mailto:knx.marketing@de.abb.com)

**Additional information and regional  
points of contact:**

[www.abb.de/knx](http://www.abb.de/knx)

[www.abb.com/knx](http://www.abb.com/knx)

---

© Copyright 2021 ABB. We reserve the right to make technical changes to the products as well as amendments to the content of this document at any time without advance notice. The agreed properties are definitive for any orders placed. ABB AG does not accept any responsibility whatsoever for potential errors or possible lack of information in this document. We reserve all rights in this document and in the subject matter and illustrations contained therein. Reproduction, transfer to third parties or processing of the content – including sections thereof – is not permitted without the prior written consent of ABB AG.

