


Temp.  
0 25 40 50 60



Shift index for long-time delay only.

MULTIPLES OF CURRENT RATING



**Molded Case Circuit Breaker E 100 LINE**

**Current Ratings**

60, 70 and 80 Amperes

**Voltage Ratings**

1 pole – 120 Vac (125 Vdc)

2 and 3 pole – 240 Vac (250 Vdc)

**Frequency Rating**

60 Hertz

Type TEB, 60-80 Amperes

Enclosure Compensated

Long-time Delay and Instantaneous

Time-current Curves

Curves show enclosure-compensated circuit breaker in open air, 40°C ambient, wired with conductors of corresponding rating, no prior load. For all other ambients, use shift index at top of sheet.

**GES6123**

**Adjustments**

Long-time delay thermal trip: not adjustable.

Instantaneous magnetic trip: not adjustable.