



Test Report				Date of issue: 20.11.2015																																																																																											
				Type: M3JM 400LA 8		Product Code: 3GJM404510-_DG																																																																																									
				Protection type: Ex d I Mb		Cert. No.: LCIE 10 ATEX 3004 X /																																																																																									
				IECEx LCI 04.0032X																																																																																											
Rating:																																																																																															
<table border="1"> <thead> <tr> <th></th> <th>V</th> <th>Hz</th> <th>kW</th> <th>r/min</th> <th>A</th> <th>cos φ</th> <th>Duty</th> </tr> </thead> <tbody> <tr> <td>3-Motor</td> <td>690</td> <td>Y 50</td> <td>315</td> <td>744</td> <td>345</td> <td>0,81</td> <td>S1</td> </tr> <tr> <td>Insul.cl.F</td> <td>400</td> <td>D 50</td> <td>315</td> <td>744</td> <td>592</td> <td>0,81</td> <td>S1</td> </tr> <tr> <td>IP66</td> <td>415</td> <td>D 50</td> <td>315</td> <td>744</td> <td>585</td> <td>0,78</td> <td>S1</td> </tr> </tbody> </table>											V	Hz	kW	r/min	A	cos φ	Duty	3-Motor	690	Y 50	315	744	345	0,81	S1	Insul.cl.F	400	D 50	315	744	592	0,81	S1	IP66	415	D 50	315	744	585	0,78	S1																																																						
	V	Hz	kW	r/min	A	cos φ	Duty																																																																																								
3-Motor	690	Y 50	315	744	345	0,81	S1																																																																																								
Insul.cl.F	400	D 50	315	744	592	0,81	S1																																																																																								
IP66	415	D 50	315	744	585	0,78	S1																																																																																								
Cold resistance				Insulation resistance at 45 °C				Overload																																																																																							
Line Ambient: 22 °C				8000 MΩ 1000 V				Torque 160% 15s																																																																																							
U ₁ - V ₁ 0,00576 Ω																																																																																															
U ₁ - W ₁ 0,00575 Ω																																																																																															
V ₁ - W ₁ 0,00576 Ω																																																																																															
				High-voltage test winding 1800 V				60 s																																																																																							
<table border="1"> <thead> <tr> <th rowspan="2">Test</th> <th rowspan="2">Torque [Nm]</th> <th colspan="2">Line</th> <th colspan="2">Input</th> <th colspan="2">Output</th> <th rowspan="2">cos φ</th> <th rowspan="2">η [%]</th> </tr> <tr> <th>U[V]</th> <th>f[Hz]</th> <th>I[A]</th> <th>P1 [kW]</th> <th>P2 [kW]</th> <th>n[r/min]</th> </tr> </thead> <tbody> <tr> <td>No load test</td> <td></td> <td>399,9</td> <td>D 50</td> <td>229,7</td> <td>4,39</td> <td></td> <td>750</td> <td>0,03</td> <td></td> </tr> <tr> <td>Locked rotor test</td> <td></td> <td>89,1</td> <td>D 50</td> <td>584,3</td> <td>18,4</td> <td></td> <td>0</td> <td>0,20</td> <td></td> </tr> <tr> <td>Thermal test (100% load)</td> <td>4043</td> <td>400,5</td> <td>D 50</td> <td>592,3</td> <td>330,0</td> <td>315,0</td> <td>743</td> <td>0,80</td> <td>95,4</td> </tr> <tr> <td>Partial load points:</td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>~75% load</td> <td>3030</td> <td>400,1</td> <td>D 50</td> <td>465,1</td> <td>246,5</td> <td>236,3</td> <td>745</td> <td>0,77</td> <td>95,8</td> </tr> <tr> <td>~50% load</td> <td>2025</td> <td>400,0</td> <td>D 50</td> <td>353,1</td> <td>164,5</td> <td>157,5</td> <td>747</td> <td>0,67</td> <td>95,7</td> </tr> <tr> <td>~25% load</td> <td>1015</td> <td>400,2</td> <td>D 50</td> <td>266,3</td> <td>83,9</td> <td>78,8</td> <td>749</td> <td>0,45</td> <td>93,9</td> </tr> </tbody> </table>										Test	Torque [Nm]	Line		Input		Output		cos φ	η [%]	U[V]	f[Hz]	I[A]	P1 [kW]	P2 [kW]	n[r/min]	No load test		399,9	D 50	229,7	4,39		750	0,03		Locked rotor test		89,1	D 50	584,3	18,4		0	0,20		Thermal test (100% load)	4043	400,5	D 50	592,3	330,0	315,0	743	0,80	95,4	Partial load points:										~75% load	3030	400,1	D 50	465,1	246,5	236,3	745	0,77	95,8	~50% load	2025	400,0	D 50	353,1	164,5	157,5	747	0,67	95,7	~25% load	1015	400,2	D 50	266,3	83,9	78,8	749	0,45	93,9
Test	Torque [Nm]	Line		Input		Output		cos φ	η [%]																																																																																						
		U[V]	f[Hz]	I[A]	P1 [kW]	P2 [kW]	n[r/min]																																																																																								
No load test		399,9	D 50	229,7	4,39		750	0,03																																																																																							
Locked rotor test		89,1	D 50	584,3	18,4		0	0,20																																																																																							
Thermal test (100% load)	4043	400,5	D 50	592,3	330,0	315,0	743	0,80	95,4																																																																																						
Partial load points:																																																																																															
~75% load	3030	400,1	D 50	465,1	246,5	236,3	745	0,77	95,8																																																																																						
~50% load	2025	400,0	D 50	353,1	164,5	157,5	747	0,67	95,7																																																																																						
~25% load	1015	400,2	D 50	266,3	83,9	78,8	749	0,45	93,9																																																																																						
Temperature rise at rated load.																																																																																															
<table border="1"> <thead> <tr> <th></th> <th>[°C]</th> <th>[K]</th> <th>Method</th> <th>Measurement method</th> </tr> </thead> <tbody> <tr> <td>Stator winding :</td> <td></td> <td>74</td> <td>1</td> <td>1 Resistance</td> </tr> <tr> <td>Frame :</td> <td></td> <td>52</td> <td>2</td> <td>2 Thermocouples</td> </tr> <tr> <td>Bearing D-end :</td> <td></td> <td>50</td> <td>2</td> <td>3 Thermometer</td> </tr> <tr> <td>Rotor :</td> <td></td> <td></td> <td>3</td> <td></td> </tr> <tr> <td>Ambient Temperature :</td> <td>25</td> <td></td> <td>2</td> <td></td> </tr> </tbody> </table>											[°C]	[K]	Method	Measurement method	Stator winding :		74	1	1 Resistance	Frame :		52	2	2 Thermocouples	Bearing D-end :		50	2	3 Thermometer	Rotor :			3		Ambient Temperature :	25		2																																																									
	[°C]	[K]	Method	Measurement method																																																																																											
Stator winding :		74	1	1 Resistance																																																																																											
Frame :		52	2	2 Thermocouples																																																																																											
Bearing D-end :		50	2	3 Thermometer																																																																																											
Rotor :			3																																																																																												
Ambient Temperature :	25		2																																																																																												
<p>These tests have been carried out on motor no. 3GF10039365B, on date 2010-10-31, which is identical in electrical design with the above.</p> <p>Manufactured and tested in accordance with rules of IEC 60034-1 and IEC 60034-2-1. PLL determined from residual loss.</p> <p>On behalf of customer</p> <p>On behalf of manufacturer</p> <p>Tested by ABB Oy, Motors and Generators, Vaasa, Finland</p> <p>Telephone +358 10 2211 Telefax +358 10 22 47372</p>																																																																																															

Computer print-out valid without signature.