


On-load tap-changer type UCGL./III, VUCGL./III, UCLL./III, UC DL./III, VUCLR./III,
 18 tap positions, linear switching.
 Min. effective No. of turns in pos. 1.
 The tap-changer is delivered set in pos. 9,
 the preceding pos. was 8.

Lindningskopplare typ UCGL./III, VUCGL./III, UCLL./III, UC DL./III, VUCLR./III,
 18 lägen, linjär koppling.
 Min antal effektiva varv i läge 1.
 Lindningskopplaren levereras inställd i läge 9,
 föregående läge var 8.

Pos. Läge	Tap selector and diverter connect	30
1	1-V-x	
2	2-H-v	
3	3-V-x	
4	4-H-v	
5	5-V-x	
6	6-H-v	
7	7-V-x	
8	8-H-v	
9	9-V-x	
10	10-H-v	
11	11-V-x	
12	12-H-v	
13	13-V-x	
14	14-H-v	
15	15-V-x	
16	16-H-v	
17	17-V-x	
18	18-H-v	



We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden. © ABB '19

The tap-changer is shown in pos. 9,
 the preceding pos. was 8.
 The tap selector is seen from above.
 Contact arm V is located above contact arm H.

Lindningskopplaren visad i läge 9,
 föregående läge var 8.
 Väljaren sedd uppifrån.
 Kontaktarm V ligger över kontaktarm H.

Continuous lines show leads included in the tap-changer. Dashed lines show leads belonging to the cleats and leads.

Heldragna linjer visar ledare som ingår i lindningskopplaren. Streckade linjer visar ledare som tillhör anslutningsdonet.

2	VUCL Added	CA	12	37
1	VUCG Added	CE	07	47
Rev Ind	Revision	Appd	Year	Week

Form No.	Sheet	Cont			
	Design checked by	Year	Week		
		Dept			
	Accepted by	Accepted for prod by	Description (English)		DATA ORIGINAL
Design checked by	Design checked by	Drawn by	Description (own language)		File name
			KOPPLINGSSCHEMA		0370-10
		Issued by	Year	Week	Lang
		COM/TKO	97	23	1
		Asea Brown Boveri		5492 0370-10	
	Rev Ind	Cont			
	-	-			