

PANEL MARKS: RNSB12B8445R

TECHNICAL SPECIFICATIONS

PANEL TYPE: ReliaGear neXT SuperBox
 QUANTITY: 1
 AMPS: 1200A
 VOLTAGE: Up to 600V
 SYSTEM: 3P3W or 3P4W
 KAIC: Up to 200 KAIC SC FULLY RATED
 MATERIAL: COPPER BUS
 PLATE: SILVER PLATE
 ENCLOSURE: NEMA 3R
 MOUNTING: SURFACE

MAIN DISCONNECT DEVICE

FEED DIR. Bottom
 TYPE: Breaker
 AMPS: 1200A
 POLES: 3

INTERIOR X-VALUES



TOTAL X BUS AVAILABLE X BUS
 32 32

OPTIONS INCLUDED

| QTY | DESCRIPTION |
|-----|-----------------------|
| 1 | Copper Bus Heat Rated |
| 1 | 47 Ckt bonded grd |

BOM

| QTY | CAT # | DESCRIPTION |
|-----|---------------|--------------|
| 1 | GDBG47AL | Ground |
| 1 | IN3212NN3H2 | Bus |
| 1 | NL1210NSTNDAL | Neutral |
| 1 | ER8445R | Enclosure |
| 1 | IF3245F | Frame |
| 1 | FT45S00135 | Front 1 of 2 |
| 1 | FT45S00225 | Front 2 of 2 |
| 1 | GC45F32NNA | Gutter |
| 9 | SR03BF | Spacer |
| 9 | SR03BB | Spacer |
| 2 | SR02BF | Spacer |
| 2 | SR02BB | Spacer |
| 1 | SR01BF | Spacer |
| 1 | SR01BB | Spacer |



- 1. FIML - FRAME MOUNTING LOCATION.
- 2. DRAWING NOT TO SCALE.
- 3. DIMENSIONS ARE IN INCHES[mm].

| PANEL INFORMATION | |
|---------------------|-----------------|
| INTERNAL DIMENSIONS | 84"X47"X11" |
| EXTERNAL DIMENSIONS | 85"X48.5"X16.7" |

PROJECT NAME :
 CUSTOMER:



PANEL ID:
 CREATED BY:
 DATE:
 REVISION NO.

PRODUCT NAME:
**ReliaGear neXT
 PANELBOARD**

DRAWING NO:
 ITEM NO:
 MARKS:
 QUOTE NO:
 SHEET:

NEUTRAL ARE PRESSURE LUGS.