


Manufacturer's statement

ACS880-01 and IE4 SynRM motor package efficiency

Drive: ACS880-01-035A-3

Motor: M3BL 160MLB, 3GBL162102-ASC, P_n 15 kW, 3000 rpm



Speed	Speed rpm	P/P _n	Package efficiency
50 %**	1500	13 %**	85.5 %
63 %	1890	25 %	88.9 %
75 %	2250	42 %	90.6 %
80 %	2400	51 %	91.0 %
91 %	2730	75 %	91.9 %
100 %**	3000	100 %**	90.9 %*


*Estimated tolerance according to IEC 60034-1:

≤150kW: 0.15 x (100 - package efficiency (%)) at the nominal point


>150kW: 0.10 x (100 - package efficiency (%)) at the nominal point

**Measurement points according to EN 50598-2

Package efficiency [%] for applications with other load characteristics:



Points of measurement



Efficiency $\eta = P2/P1$

Efficiency measurements were made at:

	ABB verification laboratory, Vaasa	X	ABB verification laboratory, Västerås
	ABB verification laboratory, Helsinki		