







								
AMP	POLE	CONTROLLER TYPE	CABINET #	LUG RANGE	WEIGHT	CENTER OF GRAVITY IN(MM)		
					LB(KG)	X	Y	Z
600A	2	SEE TABLE A	F-2050MP	QTY 2 2 AWG-600 KCMIL	278(126)	13.7 (348)	30.1 (764)	10.3 (262)
	3				284(129)			
	4				290(132)			

TYPE	TRANSITION	LEVEL	PART NO.
ZTX	OPEN	2	OXAM11-L2
ZTG	OPEN	3	OXAM11-L3
ZTGD	DELAYED	3	OXBM11-L3



NOTES



1. ENCLOSURE : NEMA-1 TYPE, FREE STANDING, FLOOR MOUNT.
2. MATERIAL: 12 GA (.105) 1018 HRS REF.
3. FINISH : ANSI 61 GREY
4. CONSTRUCTION PER UL 1008 STANDARD.
5. FRONT ACCESSIBLE UNIT. NO SIDE OR REAR ACCESS REQUIRED.
6. SUITABLE WIRE BENDING SPACE PROVIDED PER THE SAFETY AGENCY STANDARDS.
7. UL AND CSA RECOGNIZED/CERTIFIED MECHANICAL LUGS ARE STANDARD.
8. EQUIPMENT GROUND LUG IS PROVIDED IN ALL UNITS. REFER SHEET 2 FOR DETAILS.
9. ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SHOWN IN INCHES(MILLIMETERS).
10. 100% RATED SOLID/SWITCHED NEUTRAL PROVIDED PER THE SWITCH CONFIGURATION.
11. SUITABLE FOR TOP AND/OR BOTTOM CABLE ENTRY.

SEISMIC NOTES:


1. BOLT ENCLOSURE FROM C-CHANNEL BASE USING THE FOLLOWING SEISMIC CERTIFIED MOUNTING HARDWARE PER MOUNTING HOLE: (HARDWARE PROVIDED BY INSTALLER).
 - *1/2-13 GRADE 5 BOLT TORQUE TO 70 FT.-LBS. (95 NEWTON METERS).
 - *1/2-13 STANDARD FLAT WASHER.
 - *1/2 (13) HELICAL SPRING LOCK WASHER.
2. CENTER OF GRAVITY DIMENSIONS ARE FOR REFERENCE ONLY.
3. FOR WORKING CLEARANCE REFER TO NATIONAL AND LOCAL CODES AND STANDARDS.

		DRAWING FILE 50C-1066	MODEL FILE 50C-1066						
		DATE MODIFIED 12-Oct-21 07:41:35 AM	DESIGNED BY DV						
Calculated for: VOLUME 0.000 in^3	CN# C126656 ⬡ Critical to Quality Characteristic	APPROVED BY SR		TITLE TruONE LAYOUT, 600A WITH NEMA-1 CABINET					
MASS 0.000 lbm	MATERIAL SPECIFICATION ----	FINISH SPECIFICATION ----		UNITS in	LOCAL TITLE -----				
UNLESS OTHERWISE SPECIFIED	MATERIAL DESCRIPTION ---			SIZE D	ROOT NUMBER 50C-1066	REV 5	RELEASE STATE In Work		
TOLERANCE ON: 1/8 DECIMALS = 0.1 2/8 DECIMALS = 0.02 3/8 DECIMALS = 0.005 ANGLES = 1.0	FINISH DESCRIPTION ---			SCALE 13:100	PRODUCT LINE ZTX/ZTG(D)			SHEET 1 of 2	


ABB PROPRIETARY AND CONFIDENTIAL INFORMATION
The information contained in this document has to be kept strictly confidential.
Any unauthorized use, reproduction, distribution or disclosure to third parties is strictly forbidden.
ABB reserves all rights. Copyright © 2024 ABB. All rights reserved.




SECTION D-D
DOOR INSIDE VIEW




SECTION A-A
LEFT VIEW
WITHOUT SIDE PANEL



SECTION B-B
TOP VIEW
WITHOUT TOP PANEL



FRONT VIEW
WITHOUT DOOR



SECTION C-C
RIGHT SIDE VIEW
WITHOUT SIDE PANEL

NOTE:
1. REFER TO SHEET (1) FOR COMPLETE NOTE DETAILS
2. MECHANICAL LUGS SHOWN IN ABOVE VIEWS ARE FOR REFERENCE ONLY.

ABB			
SIZE D	NUMBER 50C-1066	REV 5	
SCALE 13:100	PRODUCT LINE ZTX/ZTG(D)	SHEET 2 of 2	