


NOTES:

1. **WARNING:** This drawing does not completely illustrate the installation methods required for hazardous locations. Prior to any installation in a Classified Hazardous Location, verify installation methods by the Control Drawing referenced on the product's name tag and national and local codes.
2. Minimum 24VDC, Maximum 30VDC
Current is limited to 140mA



REF: N/A

	TOTALFLOW	ACTION	DOC TYPE	TITLE	DWG NO.	REV	SHEET
	Products	D23802	UD	24VDC CHARGER VOLTAGE ADAPTER TO UFLO (2100767 BOARD)	2103939	AB	1 OF 1