# Voltage monitoring relays CM-ESS.1 for single-phase AC/DC voltages

For the monitoring of voltages in single-phase AC/DC systems, ABB's CM range comprises a wide selection of powerful and compact devices, all featuring only 22.5 mm (0.89 in) width.

This range includes voltage monitoring relays for over- and undervoltage protection from 3 V to 600 V.

Incorporating ABB's long-term experience, the CM range provides your electric installation with the highest safety and reliability.



#### **Characteristics**

- Monitoring of DC and AC voltages from 3-600 V
- TRMS measuring principle
- One device includes 4 measuring ranges
- Over- or undervoltage monitoring configurable
- Hysteresis adjustable from 3-30 %
- 3 supply voltage versions
- 1 c/o contact
- 22.5 mm (0.89 in) width
- 3 LEDs for indication of operational states

## **Approvals**

€ UL 508, CAN/CSA C22.2 No.14

**⑥** GL

(pending)

**®** GOST

CB Scheme

© CCC

RMRS

#### Marks

CE CE

C-Tick

#### Order data

#### Voltage monitoring relays

Туре	Rated control supply voltage	Measuring ranges	Order code
CM-ESS.1	24-240 V AC/DC	3-30 V, 6-60 V, 30-300 V, 60-600 V	1SVR 430 830 R0300
	110-130 V AC		1SVR 430 831 R0300
	220-240 V AC		1SVR 430 831 R1300

#### Accessories

Туре	Description	Order code
ADP.01	Adapter for screw mounting	1SVR 430 029 R0100
MAR.02	Marker label for devices with DIP switches	1SVR 430 043 R0000
COV.01	Sealable transparent cover	1SVR 430 005 R0100



#### **Functions**

#### Operating controls



- 1 Adjustment of the hysteresis
- 2 Adjustment of the threshold value
- 3 Indication of operational states

U/T: green LED - control supply voltage

R: yellow LED - relay status

U: red LED - over- / undervoltage

- 4 Adjustment of the measuring range
- 5 DIP switches (see DIP switch functions)

#### Application

Depending on the configuration, the voltage monitoring relays CM-ESS.1 can be used for over- or undervoltage monitoring in single-phase AC and/or DC systems. The devices work according to the open-circuit principle.

#### Operating mode

The voltage monitoring relay CM-ESS.1 has 1 c/o contact. One device includes 4 measuring ranges: 3-30 V, 6-60 V, 30-300 V, and 60-600 V.


The unit is adjusted with potentiometers and switches on the top of the unit. The selection of over- or undervoltage monitoring is made with a DIP switch. Potentiometers, with direct reading scale, allow the adjustment of the threshold value U and of the hysteresis %. The hysteresis % is adjustable within a range of 3 to 30 % of the threshold value.

## Function diagram: overvoltage monitoring

The voltage to be monitored (measured value) is applied to terminals B-C. The supply voltage applied to terminals A1-A2 is displayed by the glowing green LED.

If the measured value exceeds the adjusted threshold value, the output relay energizes and the red LED (overvoltage) and the yellow LED (relay energized) glow.

If the measured value drops below the threshold value minus the adjusted hysteresis, the output relay de-energizes and the red and yellow LEDs turn off.




## Function diagram: undervoltage monitoring

The voltage to be monitored (measured value) is applied to terminals B-C. The supply voltage applied to terminals A1-A2 is displayed by the glowing green LED.

If the measured value drops below the adjusted threshold value, the output relay energizes, the red LED flashes  $\sqcap$ (undervoltage) and the yellow LED (relay energized) glows.

If the measured value exceeds the threshold value plus the adjusted hysteresis, the output relay de-energizes and the red and yellow LEDs turn off.



## Connection diagram

A1 11 <sub>15</sub> C  B  B  11 <sub>15</sub> C  A1 A2 12 <sub>16</sub> 14 <sub>18</sub> 14 <sub>18</sub> 12 <sub>16</sub> A2	A1-A2 B-C 11 <sub>15</sub> -12 <sub>16</sub> /14 <sub>18</sub>	Control supply voltage  Measuring range: 3-30 V, 6-60 V, 30-300 V, 60-600 V  Output contact - open-circuit principle
---	--	--

#### DIP switch functions

Position	2 1	ıΩ	1	ON	Undervoltage monitoring
ON †	<b>→</b>	275 F0005	OFF	OFF = Default	Overvoltage monitoring
OFF	<b>✓</b>	2CDC 252 2			
		7			

## Technical data

Data at  $\rm T_a$  = 25  $^{\circ}\rm C$  and rated values, unless otherwise indicated

## Input circuit

Supply circuit		A1-A2			
Rated control supply voltage U <sub>S</sub>		110-130 V AC	220-240 V AC	24-240 V AC/DC	
Rated control supply voltage tolerance		-15+10 %			
Rated frequency		50/	50/60 Hz 50/60 Hz or D0		
Current / power consumption 24	V DC	-	-	30 mA / 0.75 W	
115 \	V AC	24 mA / 2.6 VA	-	17 mA / 1.9 VA	
230 \	V AC	-	12 mA / 2.6 VA	11 mA / 2.6 VA	
On-period		100 %			
Power failure buffering time		20 ms			
Transient overvoltage protection		varistors			
Measuring circuit		B-C			
Monitoring function		over- or undervo	tage monitoring co	nfigurable	
Measuring method		TRMS measuring	principle		
Measuring inputs terminal conne	ction	B-C			
measuring r	ange	3-30 V, 6-60 V, 3	0-300 V, 60-600 V		
input resist	ance	600 kΩ			
pulse overload capacity t	< 1 s	800 V			
continous cap	acity	660 V			
Threshold value		adjustable within	the indicated meas	suring range	
Tolerance of the adjusted threshold value		10 % of the range	e end value		
Hysteresis related to the threshold value		3-30% adjustable			
Measuring signal frequency range		DC / 15 Hz - 2 k	Hz	<b>.</b>	
Rated measuring signal frequency range		DC / 50-60 Hz			
Maximum response time	AC	80 ms			
	DC	120 ms		<b>.</b>	
Accuracy within the control supply voltage tolerance		<b>Δ</b> U ≤ 0.5 %			
Accuracy within the temperature range		<b>Δ</b> U ≤ 0.06 % / °C	;		
Transient overvoltage protection		varistors			
Timing circuit					
Delay time T <sub>V</sub>		none			
Repeat accuracy (constant parameters)		±0.07% of full so	ale		
Tolerance of the adjusted delay time		-			
Accuracy within control supply voltage tolerance		-			
Accuracy within temperature range		-			

## Indication of operational states

Control supply voltage	U/T: green LED : control supply voltage applied
	2 2. Control cappily Voltago applica
Measured value	U: red LED : overvoltage
	☐☐☐: undervoltage
Relay status	R: yellow LED : relay energized

## Output circuits

Kind of output	relay, 1 c/o contact	
Operating principle		open-circuit principle (output relay energizes if the measured value exceeds 🔀 / falls below 🔂 the adjusted threshold value)
Contact material		AgNi
Rated operational voltage U <sub>e</sub> (VDE 0110,	IEC/EN 60947-1)	250 V
Minimum switching voltage / minimum sw	vitching current	24 V / 10 mA
Maximum switching voltage / maximum s	switching current	250 V AC / 4 A AC
Rated operational current I <sub>e</sub>	AC12 (resistive) at 230 V	4 A
(IEC/EN 60947-5-1)	AC15 (inductive) at 230 V	3 A
	DC12 (resistive) at 24 V	4 A
	DC13 (inductive) at 24 V	2 A
AC rating (UL 508)	utilization category (Control Circuit Rating Code)	В 300
	max. rated operational voltage	300 V AC
	max. continuous thermal current at B 300	5 A
	max. making/breaking apparent power (Make/Break) at B 300	3600/360 VA
Mechanical lifetime		30 x 106 switching cycles
Electrical lifetime (AC12, 230 V, 4 A)		0.1 x 10 <sup>6</sup> switching cycles
Maximum fuse rating to achieve	n/c contact	6 A fast-acting
short-circuit protection	n/o contact	10 A fast-acting

## General data

MTBF		available on request
Dimensions (W x H x D)	product dimensions	22.5 x 78 x 100 mm (0.89 x 3.07 x 3.94 in)
	packaging dimensions	81 x 106 x 26 mm (3.19 x 4.17 x 1.02 in)
Weight	net weight	version 24-240 V AC/DC: 0.125 kg (0.276 lb)
		version 110-130 V AC: 0.153 kg (0.337 lb)
		version 220-240 V AC: 0.154 kg (0.339 lb)
	gross weight	version 24-240 V AC/DC: 0.148 kg (0.326 lb)
		version 110-130 V AC: 0.175 kg (0.386 lb)
		version 220-240 V AC: 0.176 kg (0.388 lb)
Material of enclosure		PA 6
Mounting		DIN rail (IEC/EN 60715)
Mounting position		any
Degree of protection	0.10.004.0	IP50
	terminals	IP20
		<u>.</u>

## Electrical connection

Wire size	fine-strand with(out) wire end ferrule	2 x 0.75-2.5 mm² (2 x 18-14 AWG)
	rigid	2 x 0.5-4 mm² (2 x 20-12 AWG)
Stripping length		7 mm (0.28 in)
Tightening torque		0.6-0.8 Nm (5.31-7.08 lb.in)

## Environmental data

Ambient temperature	•	-20+60 °C
	storage	-40+85 °C
Damp heat (IEC 60068-2-30)		55 °C, 6 cycle
Vibration (sinusoidal) (IEC/EN 60255-21-1)		class 2
Shock (IEC/EN 60255-21-2)		class 2

#### Isolation data

Rated insulation voltage	supply / measuring circuit / output	600 V
(VDE 0110, IEC/EN 60947-1, IEC/EN 60255-5)	supply / output 1 / output 2	250 V
Rated impulse withstand voltage U <sub>imp</sub>	supply / measuring circuit / output	6 kV 1.2/50 μs
(IEC/EN 60947-1, IEC/EN 60255-5)	supply / output 1 / output 2	4 kV 1.2/50 μs
Test voltage between all isolated circuits	rated insulation voltage 250 V	2.0 kV, 50 Hz
(routine test)	rated insulation voltage 600 V	2.5 kV, 50 Hz
Pollution degree (VDE 0110, IEC 664, IEC/EN 602	3	
Overvoltage category (VDE 0110, IEC 664, IEC/EN	Ш	

## Standards


Product standard	IEC/EN 60255-6
Low Voltage Directive	2006/95/EC
EMC Directive	2004/108/EC
RoHS Directive	2002/95/EC

# Electromagnetic compatibility


Interference immunity to		IEC/EN 61000-6-2
electrostatic discharge	IEC/EN 61000-4-2	
radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	
electrical fast transient / burst	IEC/EN 61000-4-4	Level 3
surge	IEC/EN 61000-4-5	
conducted disturbances, induced by	IEC/EN 61000-4-6	
radio-frequency fields		
Interference emission		IEC/EN 61000-6-3
high-frequency radiated	IEC/CISPR 22, EN 55022	Class B
high-frequency conducted	IEC/CISPR 22, EN 55022	Class B

## **Technical diagrams**


## Load limit curves




AC load (resistive)



Derating factor F for inductive AC load




DC load (resistive)




Contact lifetime

#### **Dimensions**


#### in mm and inches




CM-ESS.1



ADP.01 - Adapter for screw mounting



MAR.02 - Marker label for devices with DIP switches



COV.01 - Sealable transparent cover

#### **Further documentation**

Document title	Document type	Document number
Electronic products and relays	Technical catalogue	2CDC 110 004 C020x
CM-ESS.1, CM-ESS.2		1SVC 437 833 M1000

You can find the documentation on the internet at www.abb.com/lowvoltage -> Control Products -> Electronic Relays and Controls -> Single Phase Monitors.

#### **CAD** system files

You can find the CAD files for CAD systems at http://abb-control-products.partcommunity.com/PARTcommunity/Portal/abb-control-products -> Low Voltage Products & Systems -> Control Products -> Electronic Relays and Controls -> Single Phase Monitors -> CM-ESx - Single Phase Monitors.

# Contact us

#### ABB STOTZ-KONTAKT GmbH

P. O. Box 10 16 80

69006 Heidelberg, Germany Phone: +49 (0) 6221 7 01-0 Fax: +49 (0) 6221 7 01-13 25 E-mail: info.desto@de.abb.com

You can find the address of your local sales organisation on the ABB home page http://www.abb.com/contacts -> Low Voltage Products and Systems

#### Note:

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB AG does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB AG.

Copyright© 2012 ABB All rights reserved