


Temp. 0 10-50 60C

Shift index for long-time delay only.

MULTIPLES OF CURRENT RATING



Molded Case Circuit Breaker E 150 Line

GES6120

Current Ratings

60, 70 and 80 Amperes

Voltage Ratings

2 and 3 pole - 600 Vac (250 Vdc)

3 Pole - (500 Vdc)

Frequency Rating

60 Hertz

Types TED, THED, 60-80 Amperes

Ambient Compensated

Long-time Delay and Instantaneous

Time-current Curves

Curves show ambient-compensated circuit breaker in open air, 10°C to 50°C ambient, wired with conductors of corresponding rating, no prior load. For all other ambients, use rating shift index at top of sheet.

Adjustments

Long-time delay thermal trip: notadjustable.
Instantaneous magnetic trip: not adjustable.