


SACE Tmax XT

IP54 per comando a maniglia rotante XT5-XT6-XT7 rinviato.
IP54 for rotary handle operating mechanism XT5-XT6-XT7 door mounted.
IP54 für drehhebelantrieb XT5-XT6-XT7 Übertragen.
IP54 par commande par poignée rotative XT5-XT6-XT7 renvoyée.
IP54 por mando giratorio XT5-XT6-XT7 reenviado.
旋转手柄操作机构IP54保护 XT5-XT6-XT7.




XT5-XT6-XT7




XT5

XT6

XT7





1




2

XT5 - XT7 3

XT6



3



	XT5	XT6	XT7
A	148 [5.83"]	217 [8.54"]	201 [7.91"]
B	162 [6.38"]	226 [8.90"]	212 [8.35"]
C	125 [4.92"]	158 [6.22"]	116 [4.57"]
D	130 [5.12"]	169 [6.54"]	123 [4.84"]
E	74 [2.91"]	108.7 [4.28"]	100.5 [3.96"]
F	81 [3.19"]	113 [4.45"]	106 [4.17"]
G	88.6 [3.49"]	93 [3.62"]	61.5 [2.42"]
H	86.1 [3.39"]	87.8 [3.46"]	58 [2.28"]
I	4 x Ø4.5 [Ø0.18"]	6 x Ø4.5 [Ø0.18"]	4 x Ø4.5 [Ø0.18"]
J	142.5 [5.61"]	142.5 [5.61"]	202 [7.95"]