




# OVR PV DIN Rail SPD OVRPV151000PTSU UL 1449 3rd Edition



## Electrical Characteristics

Type of networks		Photovoltaic - DC side
Number of poles / Type of current		3 / DC
Type / Test class		UL 1449 3rd Ed. - Type 1 IEC 61 643-11 - T2 / II
Maximum continuous operating voltage ( $U_{SPV}$ )	V	1000
Voltage protection level ( $U_{res}$ @ 3kA/5kA/10kA; L+/G, L-/G, L+/L-)	kV	3.4 / 3.6 / 4.0
Voltage protection rating VPR (L+/G, L-/G, L+/L-)	kV	4.0 / 4.0 / 4.0
Nominal discharge current ( $I_n$ @ 8/20)	kA	5
Maximum discharge current ( $I_{max}$ @ 8/20)	kA	15
Follow current interrupt rating ( $I_f$ )	A	None
Response time	ns	< 25
Ground residual current ( $I_{gr}$ )	$\mu$ A	< 50
Short circuit withstand ( $I_{scVPR}$ )	kA	10
Integrated thermal disconnecter		Yes
State indicator		Yes
Safety reserve		No
Remote indicator		Yes
Overcurrent protection $\text{\textcircled{O}}$		
Circuit breaker - B or C curve	A	Not required
Class J fuse	A	Not required
$\text{\textcircled{O}}$ UL approved without overcurrent protection. If continuity of service is preferred, a 10A $g_{PV}$ fuse is recommended.		
<b>Mechanical Characteristics</b>		
Wire range - solid wire	AWG	4-14
Wire range - stranded wire	AWG	6-14
Stripping length	in	0.5
Tightening torque	in-lbs	24.5
<b>Remote Indicator</b>		
Type of contact		1 NO / 1 NC
Minimum load		12 VDC / 10 mA
Maximum load		250 VAC / 1 A
Connection cross section	AWG	16
<b>Miscellaneous Characteristics</b>		
Degree of protection		NEMA 1 / IP 20
Operating temperature	F	-40° to 176°
Maximum relative humidity	%	93
Maximum altitude	ft	6562
Weight	lb	0.75
Color of housing / Fire resistance according to UL 94		Gray RAL 7035 / V-0
Reference standards		UL 1449 3rd Ed / IEC 61 643-11 / UTE C 61-740-51
<b>Replacement Cartridges</b>		
Phase		OVRPV151000CU

# Contact Us

**ABB Inc.**

Low Voltage Control Products  
16250 W. Glendale Drive  
New Berlin, WI 53151  
Phone: 888-385-1221  
Fax: 800-726-1441

**USA Technical Support & Customer Service:**

888-385-1221, Option 4  
7:30AM to 5:30PM, CST,  
Monday - Friday  
[lvps.support@us.abb.com](mailto:lvps.support@us.abb.com)

Web: [www.abb.us/lowvoltage](http://www.abb.us/lowvoltage)