


TECHNICAL DATA SHEET

PMAJACK - SRER - Termination

Terminations for braided hose

PMA**Applications:**

- In combination with PMAJACK braided hoses

Features & Benefits:

- Offers excellent termination for braids
- For PMAJACK sizes 50 - 70 available in both round and rectangular versions

Materials:

- High-grade, specially formulated polyamide 6

Compatible with:

- PMAJACK braids

Colour:

- Grey

Chemical properties:

- Please refer to www.pma.ch
(Technical Information / Chemical Resistance)


Environmental properties:

- Free from halogens and cadmium
- RoHS and REACH compliant


Product selection:												
Part no.	Conduit size	Dimensions in mm (nom.)									Weight	Packing unit
grey	NW	AI	AA	BI	BA	G	L	H	S	C	kg/100 pcs	pcs/PU
SRER-06	6	6.5	13.0	-	-	33.0	21.0	13	13.0	6.0	0.2	50
SRER-16	16	16.0	24.0	-	-	39.0	25.0	15	15.0	7.0	0.6	50
SRER-21	21	22.0	32.0	-	-	43.0	29.0	20	15.0	7.0	1.1	50
SRER-29	29	30.0	40.0	-	-	43.0	29.0	18	39.0	7.0	1.5	50
SRER-50	50	50.0	61.0	-	-	43.0	29.0	18	50.0	7.0	2.4	20
SREV-40	40	47.0	58.0	34.0	44.0	44.0	24.0	20	38.0	10.0	2.1	20

Our customer service dept. or local distribution partner will be pleased to help you concerning product availability and lead time


SRER NW06 - 21



SRER NW29 + 50



SREV NW40



Mechanical Properties:	Value:	Test parameters:	Test method:
Tensile modulus	1'200 ... 3'700 N/mm ²		ISO 527
Tensile strength	45 ... 65 N/mm ²		ISO 527
Notched bar impact test	4 ... 20 kJ/m ²		ISO 180/1C
Vibration and shock standard	Cat. 2	IEC 61373, IEC 60068-2-27 / -64	

Thermal properties:	Value:	Test parameters:	Test method:
Continuous application temperature	- 50 ... +105 °C		PMA DO 9.21-4510
Upper application temperature	+ 120°C	(20'000 h)	PMA DO 9.21-4360
Short-term	+ 160°C	(168 h)	PMA DO 9.21-4360

Fire safety properties:	Value:	Test parameters:	Test method:
Fire performance	non flame-propagating		IEC EN 61386-1
Flame class	V0		UL 94
Fire hazard level	HL3		EN 45545-2 (R22)
Oxygen index	> 32 %		EN ISO 4589-2
Smoke density	< 150 Ds max.		EN ISO 5659-2 (25 kW/m ²)
Toxicity	< 0.75 CIT _{NLP}		NF X 70-100-1/-2: (600°C)
Fire hazard level	HL3		EN 45545-2 (R23)
Oxygen index	> 32 %		EN ISO 4589-2
Smoke density	< 300 Ds max.		EN ISO 5659-2 (25 kW/m ²)
Toxicity	< 1.5 CIT _{NLP}		NF X 70-100-1/-2: (600°C)
Fire performance NFPA 130:			NFPA 130
- Flammability	compliant		ASTM E 162
- Smoke density	compliant		ASTM E 662
Heat and visible smoke	26.00 MJ/kg		ASTM E 1354
Smoke emission toxicity	compliant		Bombardier SMP 800-C
Smoke emission toxicity	compliant		Boeing BSS 7241

The SRE2 bushing of NW16 & NW21 do not comply with NFPA 130 and UL94

Content of delivery:

- Termination for braided hose, including bushing (SRE2)

ABB Switzerland Ltd,
PMA Cable Protection
Aathalstrasse 90
8610 Uster, Switzerland
Phone: +41 58 585 00 11
pma-info@ch.abb.com
www.pma.ch

Let's write the future.
Together. **abb.com**

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB Installation Products Inc. does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB Inc. Copyright© 2019 ABB Installation Products Inc. All rights reserved

